

DA 2578

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



- Customised kitchen design – fully integrated in 702 mm width
- Unique user convenience – Con@ctivity
- Powerful – 600 m³/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover

EAN: 4002515978276 / Material number: 10851350 / Old Material Number: 28257855GB

Construction type	
Integrated extractor	•
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKF 15-P
Design	
Colour	Stainless steel
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A
Annual energy consumption in kWh/year	51,7
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	B
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	2 x 3 W
Light intensity in lx	300 lx
Colour temperature in K	3000 Kelvin
Fan	
Dual-action fan	•
AC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	250
Air throughput in Level 2 (m ³ /h) according to EN 61591	300
Air throughput in Level 3 (m ³ /h) according to EN 61591	360
Air throughput in Booster level (m ³ /h) according to EN 61591	600
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	51,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	56,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	67,0

DA 2578

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515978276 / Material number: 10851350 / Old Material Number: 28257855GB

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	41,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	52,0
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	250
Air throughput in Level 3 (m ³ /h) according to EN 61591	320
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	530
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	55,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	59,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	63,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	72,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	44,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	57,0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	702
Canopy height in mm	50
Canopy depth in mm	402
Minimum height above electric hobs in mm	450
Net weight in kg	11,6
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0,22
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Combination with WiFi-enabled Miele hob	recommended

DA 2578

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515978276 / Material number: 10851350 / Old Material Number: 28257855GB

Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Ja