


APFD 400

Holder

for the safe reprocessing of feeding cup lids.



- For safe positioning of the load on the cup rack
- Can accommodate 6 feeding cup lids securely
- For use in the upper basket of PG 805x/809x dishwasher series

EAN: 4002515986905 / Material number: 10869860 / Old Material Number: 67540001D

Product classification	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8091	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
Product category	
Other inserts	•
Product properties	
Material	Wire, rilsan-coated
Colour	White
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	53
External dimensions, net width in mm	451
External dimensions, net depth in mm	89
External dimensions, gross height in mm	95
External dimensions, gross width in mm	170
External dimensions, gross depth in mm	550
Net weight in kg	0,23
Gross weight in kg	0,41