

H 2850 B

Oven

seamless design with clear text display and PerfectClean.



- 7-segment display with retractable rotary controls – EasyControl
- Particularly easy to clean – PerfectClean finish
- Lots of room and flexibility – 76 l oven capacity on 5 levels
- Protects against burns – touch-cool fronts
- Fewer fingerprints and easy to clean – CleanSteel

EAN: 4002516156758 / Material number: 11093310 / Old Material Number: 22285044GB

| Construction type and design                                          |                             |
|-----------------------------------------------------------------------|-----------------------------|
| Built-in oven                                                         | •                           |
| PureLine                                                              | •                           |
| Appliance Colour                                                      | Stainless steel/Clean Steel |
| Retractable rotary controls                                           | •                           |
| Convenience features                                                  |                             |
| Rapid heat-up                                                         | •                           |
| Operating modes                                                       |                             |
| Defrosting                                                            | •                           |
| Eco hot air                                                           | •                           |
| Grill operating modes                                                 | •                           |
| Grill                                                                 | •                           |
| Fan plus                                                              | •                           |
| Intensive bake                                                        | •                           |
| Conventional heat                                                     | •                           |
| Bottom heat                                                           | •                           |
| Fan grill                                                             | •                           |
| User convenience                                                      |                             |
| Display                                                               | EasyControl                 |
| SoftOpen                                                              | •                           |
| SoftClose                                                             | •                           |
| Individual settings                                                   | •                           |
| Time of day display                                                   | •                           |
| Minute minder                                                         | •                           |
| Programmable end of cooking duration                                  | •                           |
| Programmable cooking duration                                         | •                           |
| Actual temperature display                                            | •                           |
| Target temperature display                                            | •                           |
| Buzzer when desired temperature is reached                            | •                           |
| Recommended temperature                                               | •                           |
| Efficiency and sustainability                                         |                             |
| Energy efficiency class (A+++ – D)                                    | A+                          |
| Cleaning convenience                                                  |                             |
| Stainless steel/CleanSteel finish                                     | •                           |
| Oven compartment with PerfectClean and catalytically enamelled liners | •                           |
| Hinged grill element                                                  | •                           |
| CleanGlass door                                                       | •                           |
| Safety                                                                |                             |
| Appliance cooling system and touch-cool front                         | •                           |
| Safety switch-off                                                     | •                           |
| System lock                                                           | •                           |
| Technical data                                                        |                             |
| Oven compartment volume in l                                          | 76                          |
| No. of shelf levels                                                   | 5                           |
| Number of shelf levels oven compartment 1                             | 5                           |
| Number of shelf levels oven compartment 2                             | 5                           |
| Numbered shelf levels                                                 | •                           |
| Oven light                                                            | 1 halogen spot              |
| Temperatures min. in °C                                               | 30                          |

H 2850 B

Oven

seamless design with clear text display and PerfectClean.




EAN: 4002516156758 / Material number: 11093310 / Old Material Number: 22285044GB

|                                               |          |
|-----------------------------------------------|----------|
| Temperatures max. in °C                       | 250      |
| Niche width min. in mm                        | 560      |
| Niche width max. in mm                        | 568      |
| Niche height min. in mm                       | 590      |
| Niche height max. in mm                       | 595      |
| Niche depth in mm                             | 550      |
| Appliance width in mm                         | 595      |
| Appliance height in mm                        | 596      |
| Temperatures in °C                            | 30–250   |
| Appliance depth in mm                         | 569      |
| Weight in kg                                  | 42,0     |
| Total rated load in kW                        | 3,50     |
| Voltage in V                                  | 220-240  |
| Frequency in Hz                               | 50       |
| Number of phases                              | 1        |
| Fuse rating in A                              | 16       |
| Length of supply lead in m                    | 1,50     |
| Replacing lamps                               | Customer |
| <b>Accessories supplied</b>                   |          |
| Universal tray with PerfectClean              | 1        |
| Baking and roasting rack without PerfectClean | 1        |
| FlexiClip runners with PerfectClean           | 0        |
| Removable side runners (pair)                 | 1        |

## H 2850 B


### Oven

seamless design with clear text display and PerfectClean.




H226x-1B/BP/E/EP/II/P, H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings, GB, AUS

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>




H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, DGC7151, installation drawings

22 mm – glass, 23.3 mm – metal




H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings

22 mm – glass, 23.3 mm – metal



H226x-1B/BP/E/EP/II/P, H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings




H226x-1B/BP/E/EP/II/P, H2x6xB/BP, H7x6xB/BP/BPX, installation drawings

If the oven is to be installed under a hob, follow the instructions for installing the hob and the height of the hob.


H226x-1B/E/I, H2x6xB, H7x6xB, installation drawings, GB, AUS

1) Mains connection cable, L=2000 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>




DG2840, DG7x40, DGC7x4x, DG7x6x, DGC7x6x, DGD7635, DGM7x4x, DO7, H28B/BP, H7x4xB/BM/BP, H7x6xB/BP, installation drawing

1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 24 mm, 5) 32.5 mm



H226x-1B/BP/E/EP/II/P, H2760B/BP, H28x0B/BP, H7x40BM/BMX, H7x6xB/BP/BPX, installation drawings




H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings

22 mm – glass, 23.3 mm – metal

H 2850 B


Oven

seamless design with clear text display and PerfectClean.



H2xxx-1 B/BP/E/I/IP, H7xxx B/BP/BM/BMX, installation drawings

22 mm – glass, 23,3 mm – metal



H2xxx-1 B/BP/E/I/IP, H7xxx B/BP/BM/BMX, installation drawings

22 mm – glass, 23,3 mm – metal