

EVS 7010

Handleless built-in vacuum drawer, 14 cm high  
for professional vacuum packing of food.



- Remains fresh for longer – storage and portioning of food
- Intense taste – marinating food
- Preparation of food for sous-vide cooking
- Easy handling – Touch controls and fully telescopic runners
- Opening the drawer couldn't be easier – Push2open

EAN: 4002516131403 / Material number: 11093400 / Old Material Number: 30701021GB

<b>Construction type and design</b>	
Built-in vacuum sealing drawer	•
PureLine	•
VitroLine	•
ArtLine	•
Handleless	•
Colour	Obsidian black
<b>Convenience features</b>	
Preparing food for sous-vide cooking	•
Longer storage life of food	•
Marinating food	•
<b>Operating modes</b>	
Vacuum sealing	•
<b>Range of applications</b>	
Vacuum sealing food	•
Marinating food	•
Dividing food into portions	•
Vacuum sealing containers	•
Resealing original packaging	•
Sealing jars	•
Vacuum sealing liquids	•
<b>User convenience</b>	
Stainless steel vacuum sealing chamber capacity in l	8,0
Minimum bag size in mm	250
Maximum bag size in mm	350
Push2open mechanism	•
Fully telescopic runners for easy loading and unloading of the warming drawer	•
Control panel with sensor controls	•
Control panel with symbols	•
Vacuumping strength min. in steps	1
Max. vacuum settings	3
LED vacuum setting indicator	•
Vacuumping strength min. for external containers in steps	1
Max. vacuum settings for external containers	3
LED vacuum setting indicator	•
Sealing duration settings	1 - 3
LED sealing duration indicator	•
Stop function	•
<b>Vacuum-sealing technology</b>	
Stainless-steel vacuum chamber	•
Pump capacity in m <sup>3</sup> /h	4
<b>Cleaning and care</b>	
Flush control panel	•
Note regarding moisture removal from the vacuum pump	•
Replaceable sealing bar	•
<b>Safety</b>	
Safety switch-off	•
<b>Technical data</b>	
Appliance width in mm	595

EVS 7010

Handleless built-in vacuum drawer, 14 cm high  
for professional vacuum packing of food.




EAN: 4002516131403 / Material number: 11093400 / Old Material Number: 30701021GB

Appliance height in mm	141
Appliance depth in mm	570
Useable interior height in mm	80
Total rated load in kW	0,32
Voltage in V	230
Frequency in Hz	50-60
Fuse rating in A	10
Number of phases	1
Mains cable with plug	•
Length of supply lead in m	1,8
<b>Accessories included</b>	
Adapter for vacuum-sealing container	1
Vacuum sealing bag support	1
Vacuum sealing bags	•
Number of vacuum sealing bags 180 x 280 mm	50
Number of vacuum sealing bags 240 x 350 mm	50

## EVS 7010

Handleless built-in vacuum drawer, 14 cm high  
for professional vacuum packing of food.




ESW7x10, DGC7x4xHCPro, DGC7x4xHCXPro, installation drawings




ESW7x10, EVS7010, DG7x4x, DGM7x4x installation drawings


A) 22 mm glass, 23,3 mm stainless steel



ESW7x10, EVS7010, DGC7x6xHCPro, DGC7x6xHCXPro installation drawings




built-in ESW7x10 EVS7010, installation drawing




built-in EVS 7010 build-under, installation drawing

1) Countertop overhang ≤ 29mm



side view ESW7x10 EVS7010, installation drawing, GB, AU



installation EVS7010 installation drawing, GB, AU

1) Mains connection cable, L=2000 mm, 2) No connection in this area, 3) Ventilation cutout min. 180 cm<sup>2</sup>