

DGM 7840

Steam oven with microwave

for healthy cooking & rapid heating-up with networking, menu cooking + M Touch.



- Large touch display with proximity sensor – M Touch + MotionReact
- Perfect results – DualSteam technology
- Consistent and quick microwave results – Quick & Gentle
- Perfect results guaranteed every time – Automatic programmes
- Shorter cooking durations by combining steam with microwave power

EAN: 4002516166672 / Material number: 11094500 / Old Material Number: 23784044GB

| | |
|---|-----------------------------|
| Construction type | |
| Appliance Colour | Stainless steel/Clean Steel |
| Construction type and design | |
| Steam oven with microwave | • |
| PureLine | • |
| Convenience features | |
| Quick & Gentle | • |
| External steam generation | • |
| Menu cooking without transfer of taste | • |
| Automatic programmes with ability to make individual adjustments | • |
| Keeping warm | • |
| Operating modes | |
| Defrosting | • |
| Automatic programmes | • |
| Country-specific automatic programmes | • |
| Steam cooking | • |
| Rapid cooking | • |
| Reheat | • |
| Microwave | • |
| Eco steam cooking | • |
| Special applications | • |
| User convenience | |
| Networking with Miele@home | • |
| Display | M Touch |
| MotionReact proximity sensor | • |
| MotionReact: light comes on when movement is detected | • |
| MotionReact: display comes on when movement is detected | • |
| MotionReact: audible signal is acknowledged when movement is detected | • |
| MotionReact: detection of cabinet fronts | • |
| SoftOpen | • |
| MultiLingua | • |
| MyMiele | • |
| Help function | • |
| Popcorn function | • |
| Quantity-independent cooking | • |
| Steam cooking on up to 3 levels at the same time | • |
| Automatic menu cooking | • |
| Steam reduction before end of programme | • |
| Polyphonic buzzers | • |
| Time of day display | • |
| Date display | • |
| Minute minder | • |
| Programmable start of cooking duration | • |
| Programmable end of cooking duration | • |
| Programmable cooking duration | • |
| Actual temperature display | • |
| Target temperature display | • |
| Buzzer when desired temperature is reached | • |

DGM 7840

Steam oven with microwave

for healthy cooking & rapid heating-up with networking, menu cooking + M Touch.



EAN: 4002516166672 / Material number: 11094500 / Old Material Number: 23784044GB

| | |
|---|-----------------|
| Recommended temperature | • |
| Quick microwave | • |
| User programmes | • |
| Individual settings | • |
| Efficiency and sustainability | |
| Power rating in off mode in W | 0,5 |
| Power rating in standby mode in W | 1,0 |
| Power rating in networked standby in W | 2,0 |
| Time until automatic switch to standby in min | 20 |
| Time until automatic switch to networked standby in min | 20 |
| Time until automatic switch to off mode in min | 20 |
| Cleaning and care | |
| Stainless steel/CleanSteel finish | • |
| Stainless-steel oven compartment with linen structure | • |
| External steam generator | • |
| Floor heater for condensate reduction | • |
| Maintenance programmes | • |
| Soak programme | • |
| Quick-release side racks | • |
| Removable stainless-steel side racks | • |
| Descaling | • |
| CleanGlass door | • |
| Steam techn./water supply | |
| DualSteam | • |
| Removal of fresh water container with Push2release | • |
| Fresh water container volume in l | 1,5 |
| Safety | |
| Appliance cooling system and touch-cool front | • |
| Safety switch-off | • |
| System lock | • |
| Vapour cooling system | • |
| Sensor lock | • |
| Technical data | |
| L – Oven compartment | • |
| Oven compartment volume in l | 40 |
| No. of shelf levels | 4 |
| Door hinge | Bottom |
| Oven light | 2 LED spots |
| Steam-cooking mode temperatures min. in °C | 40 |
| Steam-cooking mode temperatures max. in °C | 100 |
| Electronically controlled microwave power | • |
| Microwave power levels in W | |
| Niche width min. in mm | 560 |
| Niche width max. in mm | 568 |
| Niche height min. in mm | 450 |
| Niche height max. in mm | 452 |
| Niche depth in mm | 550 |
| Appliance dimensions (W x H x D) in mm | 595 x 455 x 569 |
| Appliance width in mm | 595 |
| Appliance height in mm | 455 |
| Appliance depth in mm | 569 |

DGM 7840

Steam oven with microwave

for healthy cooking & rapid heating-up with networking, menu cooking + M Touch.



EAN: 4002516166672 / Material number: 11094500 / Old Material Number: 23784044GB

| | |
|----------------------------|---------|
| Weight in kg | 30,6 |
| Total rated load in kW | 3,30 |
| Voltage in V | 230 |
| Frequency in Hz | 50 |
| Fuse rating in A | 16 |
| Number of phases | 1 |
| Mains cable with plug | • |
| Length of supply lead in m | 2 |
| Replacing lamps | Service |

Accessories included

| | |
|---|---|
| Removable side runners (pair) | 1 |
| No. of perforated stainless-steel cooking container | 2 |
| Solid stainless steel cooking containers DGG 50 40 | 1 |
| Solid stainless steel cooking containers DGG 50 80 | 1 |
| Wire rack | 1 |
| Glass tray DMGS 7 100 30 | 1 |
| Descaling tablets | 2 |

Available display languages


Available display languages via MultiLingua

bahasa malaysia, dansk,
deutsch, english, español,
français, hrvatski, italiano,
magyar, nederlands,
norsk, polski, portugês,
русский, română,
slovenčina, slovenščina,
srpski, suomi, svenska,
türkçe, українська, čeština,
ελληνικά,

DGM 7840


Steam oven with microwave

for healthy cooking & rapid heating-up with networking, menu cooking + M Touch.




DG2840, DG7x40, DGC7x4x, DG7x6x, DGC7x6x, DGD7635, DGM7x4x, DO7, H28B/BP, H7x4xB/BM/BP, H7x6xB/BP, installation drawing


1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 24 mm, 5) 32.5 mm



ESW7x20, DGC7x4xHCPro, DGC7x4xHCXPro installation drawings




ESW7x20, DG7xxx, DGM7xxx installation drawings




ESW7x20, DGM7x4x installation drawings

1) Front view, 2) Mains connection cable, L=2.000 mm, 3) Ventilation cut min. 180 cm², 4) No connection in this area




ESW7x10, DGC7x4xHCPro, DGC7x4xHCXPro, installation drawings




ESW7x10, EVS7010, DG7x4x, DGM7x4x installation drawings


A) 22 mm glass, 23,3 mm stainless steel



DG7xxx, DGM7xxx, installation drawings



built-in DG DGM DGC XL build-under, installation drawing




Screw joint DG DGM, installation drawing


DGM 7840

Steam oven with microwave

for healthy cooking & rapid heating-up with networking, menu cooking + M Touch.




DG DGM, installation drawing



side view DG DGM, installation drawing, GB, AU

22 mm glass, 23,3 mm stainless steel



installation DGM, installation drawing, GB, AU

1) Mains connection cable, L=2000 mm, 2) Water supply hose, L=2000 mm, 3) ventilation cut-out min. 180 cm^2 , 4) no connection in this area