

KS 28463 D ed/cs

Freestanding refrigerator

With PerfectFresh Pro and FlexiLight for longer freshness and optimum lighting.



- Food stays fresh for up to 5 x longer with PerfectFresh Pro
- Individually adjustable glass shelf lighting thanks to FlexiLight
- Door shelves can be cleaned in the dishwasher – ComfortClean

EAN: 4002516122357 / Material number: 11127610 / Old Material Number: 36284635AUS

|  |                            |
|--|----------------------------|
| <b>Appliance category</b>                                      |                            |
| Refrigerator   | •                          |
| <b>Construction type</b>                                       |                            |
| Freestanding appliance   | •                          |
| Door hinge   | right                      |
| Convertible door hinging                                       | •                          |
| Side-by-side enabled   | •                          |
| <b>Design</b>  |                            |
| Casing colour  | Stainless steel CleanSteel |
| Front colour   | Stainless steel/CleanSteel |
| Refrigeration section lighting                                 | FlexiLight                 |
| PerfectFresh Pro LED lighting                                  | •                          |
| <b>User convenience</b>  |                            |
| Networking with Miele@home                                     | •                          |
| Accessories required   | XKS 3100 W                 |
| Freshness system   | PerfectFresh Pro           |
| ComfortClean   | •                          |
| DynaCool   | •                          |
| XL interior  | •                          |
| SoftClose  | •                          |
| SelfClose  | •                          |
| Concealed door opener  | Click2open                 |
| Silence system   | •                          |
| <b>Controls</b>  |                            |
| Operating concept  | FreshTouch                 |
| Fridge compartment can be switched off                         | No                         |
| Independent temperature regulation of fridge and freezer zones | No                         |
| Automatic SuperCool  | •                          |
| No. of temperature zones                                       | 2                          |
| Sabbath mode   | •                          |
| Party mode   | •                          |
| Holiday mode   | •                          |
| QuickCool Timer  | •                          |
| <b>Fridge/Fridge section</b>                                   |                            |
| No. of shelves   | 4                          |
| of which illuminated   | 2                          |
| Chrome-plated metal bottle rack                                | •                          |
| No. of crisper drawers   | 3                          |
| Half-width door shelves  | 2                          |
| Door rack for bottles  | 2                          |
| <b>Safety</b>  |                            |
| Lock function  | •                          |
| Acoustic door alarm  | •                          |
| Optical door alarm   | •                          |
| <b>Technical data</b>  |                            |
| Appliance width in mm  | 600                        |
| Appliance height in mm   | 1850                       |
| Appliance depth in mm  | 675                        |
| Weight in kg   | 77,7                       |

KS 28463 D ed/cs

Freestanding refrigerator

With PerfectFresh Pro and FlexiLight for longer freshness and optimum lighting.



EAN: 4002516122357 / Material number: 11127610 / Old Material Number: 36284635AUS

|                                    |                  |
|------------------------------------|------------------|
| Climate class                      | SN-T             |
| including PerfectFresh zone in l   | 133              |
| Total usable capacity in l         | 367              |
| Storage time in case of fault in h | 0                |
| Current consumption (mA)           | 1200             |
| Voltage in V                       | 220-240          |
| Fuse rating in A                   | 10               |
| Number of phases                   | 1                |
| Frequency in Hz                    | 50               |
| Length of supply lead in m         | 2,0              |
| Replacing lamps                    | Customer Service |
| <b>Accessories supplied</b>        |                  |
| Butter dish                        | •                |
| Egg tray                           | •                |