

## KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



- Intuitive quick selection via number sequences – Smart Select
- 4 cooking zones incl. 2 powerful PowerFlex cooking areas
- A width of 916 mm for surface-mounted or flush-fit installation
- Shortest heating-up times – TwinBooster
- Communication with the cooker hood – automatic Con@ctivity function


EAN: 4002516149293 / Material number: 11144070 /  
Old Material Number: 26768470GB

General information	
Model identifier	KM 7684 FL
Manufacturer material number	11144070
EAN number	4002516149293
Marketing class	Platinum
Heating type	
Heating type	Induction
Construction type	
Independent of cooker	•
Design	
Elegant glass ceramic surface	•
Ceramic surface colour	Black
Flush	•
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	4
Number of cooking areas	2
Maximum number of pans	4
PowerFlex cooking zones	
No.	4
Type	PowerFlex cooking zone
Size in mm	Ø 150 – 230
Max. rating in W	2100
Max. Booster power rating in W	3000
Max. TwinBooster power rating in W	3650
1st cooking zone/cooking area	
Position	Left
Type	PowerFlex bridge
Size in mm	230x390
Max. rating in W	3400
Max. Booster power rating in W	4800
Max. TwinBooster power rating in W	7300
2nd cooking zone/cooking area	
Position	right
Type	PowerFlex bridge
Size in mm	230x390
Max. rating in W	3400
Max. Booster power rating in W	4800
Max. TwinBooster power rating in W	7300
User convenience	
Networking with Miele@home	•
Con@ctivity	•
Pan and pan size recognition	•
Operation via sensor controls	SmartSelect
Display colour	Yellow
Permanent pan recognition	•
Stop & Go function	•
Wipe protection	•

## KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.




EAN: 4002516149293 / Material number: 11144070 /  
Old Material Number: 26768470GB

Recall function	•
Minute minder	•
Safety switch-off	•
Auto heat-up	•
Keeping warm	•
Individual setting options (e.g. buzzers)	•
<b>Efficiency</b>	
Power rating in off mode in W	0,5
Power rating in standby mode in W	0,8
Power rating in networked standby in W	2,0
Time until automatic switch to off mode in min	10
Time until automatic switch to standby in min	10
Time until automatic switch to networked standby in min	10
<b>Cleaning and care</b>	
Easy to clean ceramic glass	•
<b>Safety</b>	
Safety switch-off	•
Lock function	•
System lock	•
Integrated cooling fan	•
Overheating protection	•
Residual heat indicator	•
<b>Technical data</b>	
Dimensions in mm (width)	916
Dimensions in mm (height)	51
Dimensions in mm (depth)	408
Casing height incl. connection box in mm	51
Cutout dimensions in mm (width) with surface-mounted installation	896 mm
Cutout dimensions in mm (depth) with surface-mounted installation	388 mm
Internal cutout dimensions in mm (width) with flush installation	896
Internal cutout dimensions in mm (depth) with flush installation	388
Weight in kg	12
External cutout dimensions in mm (width) with flush installation	920
External cutout dimensions in mm (depth) with flush installation	412
Total rated load in kW	7,30
Length of supply lead in m	1,4
Voltage in V	230
Frequency in Hz	50-60
<b>Accessories included</b>	
Mains cable	Yes

## KM 7684 FL


Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



KM7684FL, KM7684-1FL, flush (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm, are enclosed loosely, 3) Stepped cut-out natural stone worktop, 4) Wood support 12 mm (not supplied)



KM7684FL, KM7684-1FL, onset installation (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm