

KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



- Intuitive quick selection via number sequences – Smart Select
- 4 cooking zones incl. 4 high-power PowerFlex cooking areas
- A width of 916 mm for surface-mounted or flush-fit installation
- Shortest heating-up times – TwinBooster
- Communication with the hood – automatic Con@ctivity function

EAN: 4002516149293 / Material number: 11144070 / Old Material Number: 26768470GB

Heating type	
Heating type	Induction
Construction type	
Independent of cooker	•
Design	
Elegant glass ceramic surface	•
Flush	•
Ceramic surface colour	Black
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	4
Number of cooking areas	2
Maximum number of pans	4
PowerFlex cooking zones	
No.	4
Type	PowerFlex cooking zone
Diameter in mm	150x230
Rating in W	2,10
Booster in W	3,00
TwinBooster in W	3650
1st cooking zone/cooking area	
Position	Left
Type	PowerFlex bridge
Size in mm	230 x 390
Max. Booster power rating in W	4800
Max. rating in W	3400
Max. TwinBooster power rating in W	7300
2nd cooking zone/cooking area	
Position	right
Type	PowerFlex bridge
Size in mm	230 x 390
Max. Booster power rating in W	4800
Max. rating in W	3400
Max. TwinBooster power rating in W	7300
User convenience	
Miele@home	•
Operation via sensor controls	Smart Select
Automatic function Con@ctivity	•
Pan and pan size recognition	•
Display colour	Yellow
Auto heat-up	•
Permanent pan recognition	•
Keeping warm	•
Stop & Go function	•
Recall function	•
Minute minder	•
Safety switch-off	•
Individual setting options (e.g. buzzers)	•
Efficiency and sustainability	
Power rating in off mode in W	0,5

KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.




EAN: 4002516149293 / Material number: 11144070 / Old Material Number: 26768470GB

Power rating in standby mode in W	1,0
Power rating in networked standby in W	2,0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
Cleaning convenience	
Easy to clean ceramic glass	•
Wipe protection	•
Safety	
Safety switch-off	•
Lock function	•
System lock	•
Integrated cooling fan	•
Overheating protection	•
Residual heat indicator	•
Technical data	
Dimensions in mm (width)	916
Dimensions in mm (height)	51
Dimensions in mm (depth)	408
Cutout dimensions in mm (width) with surface-mounted installation	896
Casing height incl. connection box in mm	51
Cutout dimensions in mm (depth) with surface-mounted installation	388
Internal cutout dimensions in mm (width) with flush installation	896
Internal cutout dimensions in mm (depth) with flush installation	388
Weight in kg	12
External cutout dimensions in mm (width) with flush installation	920
External cutout dimensions in mm (depth) with flush installation	412
Total rated load in kW	7,30
Length of supply lead in m	1,4
Voltage in V	230
Frequency in Hz	50-60
Accessories supplied	
Number of mains cables with plug	Yes

KM 7684 FL


Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



KM 7684 FL – flush (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm, are enclosed loosely, 3) Stepped cut-out natural stone worktop, 4) Wood support 12 mm (not supplied)



KM 7684 FL – onset installation (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm