

## KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



- Intuitive quick selection via number sequences – Smart Select
- 4 cooking zones incl. 2 high-power PowerFlex cooking areas
- A width of 916 mm for surface-mounted or flush-fit installation
- Shortest heating-up times – TwinBooster
- Communication with the cooker hood – automatic Con@ctivity function

EAN: 4002516149293 / Material number: 11144070 / Old Material Number: 26768470GB

<b>Heating type</b>	
Heating type	Induction
<b>Construction type</b>	
Independent of cooker	•
<b>Design</b>	
Elegant glass ceramic surface	•
Flush	•
Ceramic surface colour	Black
Surface-mounted installation	•
<b>Cooking zone details</b>	
Number of cooking zones	4
Number of cooking areas	2
Maximum number of pans	4
<b>PowerFlex cooking zones</b>	
No.	4
Type	PowerFlex cooking zone
Diameter in mm	Ø 150 – 230
Rating in W	2100
Booster in W	3000
TwinBooster in W	3650
<b>1st cooking zone/cooking area</b>	
Position	Left
Type	PowerFlex bridge
Size in mm	230x390
Max. Booster power rating in W	4800
Max. rating in W	3400
Max. TwinBooster power rating in W	7300
<b>2nd cooking zone/cooking area</b>	
Position	right
Type	PowerFlex bridge
Size in mm	230x390
Max. Booster power rating in W	4800
Max. rating in W	3400
Max. TwinBooster power rating in W	7300
<b>User convenience</b>	
Miele@home	•
Operation via sensor controls	Smart Select
Automatic function Con@ctivity 3.0	•
Pan and pan size recognition	•
Display colour	Yellow
Auto heat-up	•
Keeping warm	•
Stop & Go function	•
Recall function	•
Safety switch-off	•
Permanent pan recognition	•
Individual setting options (e.g. buzzers)	•
Wipe protection	•
Minute minder	•

KM 7684 FL

Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.




EAN: 4002516149293 / Material number: 11144070 / Old Material Number: 26768470GB

<b>Efficiency and sustainability</b>	
Power rating in off mode in W	0,5
Power rating in standby mode in W	1,0
Power rating in networked standby in W	2,0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
<b>Cleaning and care</b>	
Easy to clean ceramic glass	•
<b>Safety</b>	
Safety switch-off	•
Lock function	•
System lock	•
Integrated cooling fan	•
Overheating protection	•
Residual heat indicator	•
<b>Technical data</b>	
Dimensions in mm (width)	916
Dimensions in mm (height)	51
Dimensions in mm (depth)	408
Cutout dimensions in mm (width) with surface-mounted installation	896
Cutout dimensions in mm (depth) with surface-mounted installation	388
Casing height incl. connection box in mm	51
Internal cutout dimensions in mm (width) with flush installation	896
Internal cutout dimensions in mm (depth) with flush installation	388
Weight in kg	12
External cutout dimensions in mm (width) with flush installation	920
External cutout dimensions in mm (depth) with flush installation	412
Total rated load in kW	7,30
Length of supply lead in m	1,4
Voltage in V	230
Frequency in Hz	50-60
<b>Accessories included</b>	
Mains cable	Yes

## KM 7684 FL


Induction hob with onset controls

panorama design with two PowerFlex cooking areas for extra convenience.



KM7684FL, KM7684-1FL, flush (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm, are enclosed loosely, 3) Stepped cut-out natural stone worktop, 4) Wood support 12 mm (not supplied)



KM7684FL, KM7684-1FL, onset installation (installation drawings)

1) Front, 2) Mains connection box with mains connection cable, L = 1440 mm