

PDR 908 [EL MAR 3N AC 400V 50-60Hz]  
 Vented dryer, electrically heated  
 Lloyd's Register approved, load size 8.0 kg.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

<b>Construction type and design</b>	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	8,0
Drum volume in l	130,00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for offshore use	•
Suitable for marine use	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour	5,50
Specific energy consumption in kWh/kg	0,50
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0,50
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0,42
Programme duration in min.	42
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	42
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	37
<b>Controls</b>	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3N~ 400V 50/60HZ
Electric heater rating in kW	6,14
Total connected load in kW	6,40
Fuse rating in A	10
<b>Possible voltage variant 1</b>	
Electrical connection	230V~ 50/60HZ
Heater rating in kW	2,90
Total connected load in kW	3,24
Fuse rating in A	16
<b>Possible voltage variant 2</b>	
Electrical connection	3~ 230V 50/60HZ
Heater rating in kW	6,14
Total connected load in kW	6,40

PDR 908 [EL MAR 3N AC 400V 50-60Hz]  
 Vented dryer, electrically heated  
 Lloyd's Register approved, load size 8.0 kg.



EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

Fuse rating in A	16
<b>Dimensions and weight</b>	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	51,5
Gross weight in kg	57
Maximum floor loading in N	920
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0,76
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
<b>Standards, certs, symbols</b>	
CE	•
Splash-proof safety rating IPX4	•
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•