

PDR 908 HP [MAR 1N AC 230V 60Hz]

Heat-pump dryers

Lloyd's Register approved, load size 8.0 kg.



- Drum volume 130.00 l, load size 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218432 / Material number: 11251190 /
Old Material Number: 52908288MAR

Construction type and version

Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	8,0
Drum volume in l	130,00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for offshore use	•
Suitable for marine use	•

Performance data

Maximum evaporation capacity in l/hour	2,60
Specific energy consumption in kWh/kg	0,20
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0,20
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0,17
Programme duration in min.	88
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	88
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	76

Control system

Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•

Standard electrical connection

Heating type	Heat pump
Electrical connection	230V~ 60HZ
Total connected load in kW	1,20
Fuse rating in A	10
Provided with plug	•

Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820

PDR 908 HP [MAR 1N AC 230V 60Hz]

Heat-pump dryers

Lloyd's Register approved, load size 8.0 kg.



EAN: 4002516218432 / Material number: 11251190 /
Old Material Number: 52908288MAR

Net weight in kg	72,0
Gross weight in kg	78
Maximum floor load in N	920

Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3,60

Features

Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•

Efficiency and sustainability

Recycling rate in %	95
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0,59
Refrigerant global warming potential in kg CO ₂ e	1430
Appliance global warming potential in kg CO ₂ e	844,00

Connection options

Payment system (optional)	•
Optical interface for service access	•
LAN/WiFi module (optional)	•

Standards, test certificates and symbols

CE	•
Splash-proof safety rating IPX4	•
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•