

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]  
 Professional washing machine, Little Giants, electric heating, drain pump  
 Lloyd's Register approved, load size 8.0 kg.



- Drum volume 73 l, load size 8.0 kg
- 22 % less water consumption and 28 % less energy consumption\*
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience w. full-touch colour display –M Touch Flex
- Thorough cleaning with professional wash programmes

\*Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516220589 / Material number: 11251280 / Old Material Number: 51908187MAR

<b>Construction type and design</b>	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Lotus white
Control panel colour	Stainless steel
Load in kg	8,0
Drum volume in l	73
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel	•
<b>Application</b>	
Suitable for offshore use	•
Suitable for marine use	•
<b>Performance data</b>	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6,40
Specific energy consumption for cold water connection in kWh/kg	0,13
Specific water consumption for hot water connection in l/kg	6,00
Specific energy consumption for hot water connection in kWh/kg	0,06
Water consumption with cold water connection in l	51,0
Energy consumption with cold water connection in kW	1,05
Programme duration in minutes with cold water connection	59
Water consumption with hot water connection in l	48,0
Energy consumption with hot water connection in kW	0,50
Programme duration in minutes with cold water and hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
<b>Controls</b>	
Control system	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 8.0 kg.



EAN: 4002516220589 / Material number: 11251280 / Old Material Number: 51908187MAR

<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3~ 440V
Heater rating in kW	4,00
Total connected load in kW	4,20
Fuse rating in A	10
<b>Possible voltage variant 1</b>	
Electrical connection	3- 400V
Heater rating in kW	3,40
Total connected load in kW	3,60
Fuse rating in A	10
<b>Possible voltage variant 2</b>	
Electrical connection	3~ 480V 50/60HZ
Heater rating in kW	4,80
Total connected load in kW	5,00
Fuse rating in A	10
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	108,0
Gross weight in kg	112
Maximum floor loading in N	2820
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,00
<b>Features</b>	
3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
Pre-ironing	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 8.0 kg.



EAN: 4002516220589 / Material number: 11251280 / Old Material Number: 51908187MAR

<b>Efficiency and sustainability</b>	
Recycling rate in %	95
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
<b>Standards, certs, symbols</b>	
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•