

DU 900

Drying unit, electric

For machines 900 mm wide & optimum internal & external drying of wash items.



- With top-box panelling; air supply via the ceiling installation
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash chamber
- Air flow rate 250 m<sup>3</sup>/h
- HEPA filter service life: 1000 hours

EAN: 4002516265153 / Material number: 11382230 / Old Material Number: 69250004USA

Product classification	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
Dimensions and weight	
External dimensions, net height in mm	840
External dimensions, net width in mm	845
External dimensions, net depth in mm	1045
External dimensions, gross height in mm	990
External dimensions, gross width in mm	845
External dimensions, gross depth in mm	1200
Net weight in kg	116,00
Gross weight in kg	133,00