

DU 1150

Drying unit, electric

For machines 1150 mm wide & optimum internal & external drying of wash items.



- With top-box panelling; air supply via the ceiling installation
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash chamber
- Air flow rate 250 m³/h
- HEPA filter service life: 1000 hours

EAN: 4002516265160 / Material number: 11382260 / Old Material Number: 69250005USA

Product classification	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8617	•
Dimensions and weight	
External dimensions, net height in mm	855
External dimensions, net width in mm	850
External dimensions, net depth in mm	1190
External dimensions, gross height in mm	1010
External dimensions, gross width in mm	850
External dimensions, gross depth in mm	1200
Net weight in kg	120,00
Gross weight in kg	137,00