

## DU 1150 RV

Drying unit, with ventilation slots, electric

For appliances 1150 mm wide and optimum internal and external drying of loads.

EAN: 4002516265184 / Material number: 11382350 / Old Material Number: 69250007USA



- With top-box panelling; air supply via the room.
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash cabinet
- Air flow rate 250 m<sup>3</sup>/h
- HEPA filter service life: 1000 hours

Product classification	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8617	•
Dimensions and weight	
External dimensions, net height in mm	855
External dimensions, net width in mm	850
External dimensions, net depth in mm	1190
External dimensions, gross height in mm	1010
External dimensions, gross width in mm	850
External dimensions, gross depth in mm	1200
Net weight in kg	120,00
Gross weight in kg	137,00