

G 7360 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Maximum convenience – 3D MultiFlex tray C with chopstick holder
- Communication with the machine could not be easier – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Fresh water dishwashers – from ?? in the Automatic programme
- Versatile and secure – ExtraComfort C basket design

EAN: 4002516282082 / Material number: 11432560 / Old Material Number: 21736062SG

Model	
Fully integrated dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	CleanSteel/Obsidian black
Control panel version	Fully integrated fascia
Control type	Softkeys
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	43
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	optical and acoustic
Display language selection	•
Efficiency and sustainability	
Drying class	A
Water consumption in the ECO programme in l	8,9
Annual water consumption in the ECO programme in l	2492
Annual energy consumption in ECO programme in kWh	192
Number of place settings	12
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
PowerWash	•
Gentle	•
Hygiene	•
SolarSave	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
Dishwashing options	
AutoDos	•
IntenseZone	•

G 7360 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.




EAN: 4002516282082 / Material number: 11432560 / Old Material Number: 21736062SG

Express	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray C
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort C
Safety	
Waterproof system	•
Filter indicator light	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	550
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	550
Depth with door open in cm	116,5
Net weight in kg	48,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Min. front panel weight in kg	4,0
Max. front panel weight in kg	11,0
[can be retrofitted by Service to min.]	7,0
[can be retrofitted by Service to max.]	14,0
Available display languages	
Available display languages via MultiLingua	english
Accessories included	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7360 C SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),