

PR 900  
 Built-in report printer  
 For printing process protocols.



- Thermal printer with 60 mm paper width
- Can be installed on the outfeed side with two-door models

EAN: 4002516362081 / Material number: 11491220 / Old Material Number: 69247004D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 8615	•
PLW 8616	•
<b>Product properties</b>	
Colour	Black
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	950
External dimensions, net width in mm	77
External dimensions, net depth in mm	69
External dimensions, gross height in mm	125
External dimensions, gross width in mm	200
External dimensions, gross depth in mm	1000
Net weight in kg	2,87
Gross weight in kg	3,59