

## DOS K 85 flex

Dispenser module for 5-10 litre canisters

with level indicator for the automatic dispensing of liquid media.



- Dispenser monitoring – high process security as per EN ISO 15883
- For dispensing liquid cleaning agent/neutralising agent
- 352 mm siphon for 5–10 l media canisters with flexible cap
- Siphon conversion kit for 10–30 l media canisters available

EAN: 4002516365280 / Material number: 11498910 / Old Material Number: 69747052USA

| Product classification                  |         |
|---|---------|
| Washer-disinfectors, laboratory         | •       |
| Thermal disinfectors                    | •       |
| Washer-disinfectors, medical            | •       |
| Machine affiliation                     |         |
| PG 8581                                 | •       |
| PG 8562                                 | •       |
| PG 8582                                 | •       |
| PG 8583                                 | •       |
| PG 8591                                 | •       |
| PG 8592                                 | •       |
| PG 8593                                 | •       |
| Product category                        |         |
| Dispenser system                        | •       |
| Product properties                      |         |
| Production rate in ml/60 s              | 55      |
| Length of suction lance in mm           | 352     |
| Standard electrical connection          |         |
| Number of phases                        | 1       |
| Neutral conductor                       | N       |
| AC/DC                                   | AC      |
| Voltage in V                            | 200-240 |
| Frequency in Hz                         | 60      |
| Total rated load in kW                  | 0,01    |
| Fuse rating in A                        | 0       |
| Dimensions and weight                   |         |
| External dimensions, net height in mm   | 0       |
| External dimensions, net width in mm    | 0       |
| External dimensions, net depth in mm    | 0       |
| External dimensions, gross height in mm | 160     |
| External dimensions, gross width in mm  | 198     |
| External dimensions, gross depth in mm  | 478     |
| Net weight in kg                        | 2,21    |
| Gross weight in kg                      | 2,43    |
| Standards, certs, symbols               |         |
| CE                                      | •       |