

CM 5510 Silence  
Countertop coffee machine  
with OneTouch for Two for the ultimate in coffee enjoyment.



- Two coffees at once at the touch of a button – OneTouch for Two
- Perfect results and intense coffee flavour – AromaticSystem
- Creamy milk froth for a wide range of coffee specialities
- Convenient cleaning and maintenance programmes
- Convenient when hosting lots of guests – coffee/tea pot function

EAN: 4002516333814 / Material number: 11525620 / Old Material Number: 29551004GBX

Construction type and design	
Freestanding bean-to-cup coffee machine	•
Colour	Rose gold PearlFinish
Convenience features	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
Programmable User profiles	2
Aroma-friendly conical grinder	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
User convenience	
Display	DirectSensor
Multilingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	200
Bean container capacity, total in g	200
Capacity of water container in l	1,3
Drip tray capacity	0,8
Easily accessible containers	•
Programmable standby time	•
Programmable settings	•
Beverages	
Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Caffè latte, single	•
Caffè latte, double	•
Hot water, single	•

CM 5510 Silence  
Countertop coffee machine  
with OneTouch for Two for the ultimate in coffee enjoyment.



EAN: 4002516333814 / Material number: 11525620 / Old Material Number: 29551004GBX

Coffee pot	•
<b>Efficiency and sustainability</b>	
Energy-saving eco-mode selectable	•
<b>Cleaning convenience</b>	
Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Programmable water hardness	•
<b>Safety</b>	
System lock	•
<b>Technical data</b>	
Height-adjustable serving spout in cm	13,5
Height-adjustable serving spout in cm	8,0
Appliance width in mm	241
Appliance height in mm	360
Appliance depth in mm	460
Total rated load in kW	1,45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Length of supply lead in m	1,2
<b>Accessories supplied</b>	
Brief operating instructions on rear of unit	•
<b>Available display languages</b>	
Available display languages through MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,