

PT 7186 Vario XL [EL SOM 3N AC 400V 50Hz]

Vented dryer, electrically heated

Specially designed for marine requirements.



- Drum volume 180.00 l, load size 9.0 kg
- Large programme variety – application-specific drying programmes
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002516335115 / Material number: 11529090 / Old Material Number: 527186XSOM

Construction type and design	
Construction type	Front loader
Range	Octoplus
Front	Stainless steel
Load in kg	9,0
Load ratio	1:20
Drum volume in l	180,00
Drying system	Exhaust air
Door opening [Ø] in mm	440
Door opening angle in degrees	180
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Maximum evaporation capacity in l/hour	8,10
Programme duration in min.	41
Controls	
Control system	Profitrronic L Vario
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard/target grp programmes	
Basic programmes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for domestic use	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	7,94
Total connected load in kW	8,50
Fuse rating in A	16
Dimensions and weight	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	763
External dimensions, gross height in mm	1215
External dimensions, gross width in mm	760
External dimensions, gross depth in mm	820
Net weight in kg	77,0
Gross weight in kg	88
Maximum floor loading in N	1000

PT 7186 Vario XL [EL SOM 3N AC 400V 50Hz]

Vented dryer, electrically heated

Specially designed for marine requirements.



EAN: 4002516335115 / Material number: 11529090 / Old Material Number: 5271860XSOM

Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,62
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Machine-independent accessories	•
Connection options	
Payment system	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Capacities	
Respirator masks [number]	4
Overalls [number]	1
Over jackets [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Down duvets [number]	1
Down pillows [number]	1-2
Cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Standards, certs, symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•