

## CM 6160 MilkPerfection Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



- Creamy milk froth for a wide range of coffee specialties
- Perfect results and intense coffee flavour – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning and maintenance programmes
- Communication with the machine could not be easier – WiFi Conn@ct

EAN: 4002516362050 / Material number: 11590180 /  
Old Material Number: 29616001GBX

### Construction type and design

Appliance colour Lotus white

### Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands, norsk,  
polski, português, русский,  
română, slovenčina,  
slovenščina, srpski, suomi,  
svenska, türkçe, українська,  
čeština, ελληνικά,  
□□□□□□□□, □□, □  
□□, □□□□□, □□□□

### Construction type and design

Freestanding bean-to-cup coffee machine

### Convenience features

AromaticSystem

OneTouch preparation

OneTouch for Two preparation

DoubleShot

Programmable User profiles

Aroma-friendly conical grinder

Selectable grinder setting

Additional coffee types in ground coffee form possible

Programmable amount of coffee

Programmable amount of water

Programmable water temperature

Amount of milk can be programmed

Programmable amount of milk froth

Pre-brewing programmable

TeaTimer

### User convenience

Networking with Miele@home

Display

PerformanceMode

BrilliantLight

Expert mode

MultiLingua

No. of bean types

No. of bean containers

Capacity of bean container A in g

Bean container capacity, total in g

Capacity of water container in l

Capacity of waste container in capsules

Drip tray capacity

Easily accessible containers

Programmable standby time

Programmable settings

## CM 6160 MilkPerfection Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



EAN: 4002516362050 / Material number: 11590180 /  
Old Material Number: 29616001GBX

### Drink specialities

Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Warm water, single	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
White tea, single	•
Japanese tea, single	•
Coffee pot	•

### Efficiency and sustainability

Energy-saving eco-mode selectable	•
Power rating in standby mode in W	0,3
Power rating in networked standby in W	1,0

### Cleaning and care

Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•

## CM 6160 MilkPerfection Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



EAN: 4002516362050 / Material number: 11590180 /

Old Material Number: 29616001GBX

Removable brew unit	•
Programmable water hardness	•
<b>Technical data</b>	
Height-adjustable serving spout in cm	14,0
Height-adjustable serving spout in cm	8,0
Appliance width in mm	251
Appliance height in mm	359
Appliance depth in mm	427
Total rated load in kW	1,45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Pump pressure in bar	15
Length of supply lead in m	1,4
<b>Accessories included</b>	
Stainless steel milk tube	•
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•