

PRI 318 [EL SOM LAM IB RF] Rotary ironer, electrically heated with leaf-spring padding, feed-in belts and return feed for marine applications.



- Performance 87.0 kg/h*, roller diameter 300 mm, working width 1750 mm
- Fast cooling of textiles EasyFold feed table
- State-of-the-art controls Touch display
- Selection of the most important settings favourite programmes
- Perfect rotary ironing performance flexibly positioned heater plate

EAN: 4002516367901 / Material number: 11607850 / Old Material Number: 53318106SOM

Construction type and version	
Construction type	Laundry infeed at the front,
on out do not have	laundry outfeed at the back
Can be set up against a wall	•
Range	Professional
Outer casing	Iron grey
Roller diameter in mm	300
Working width in mm	1750
Heater plate material	Aluminium
Padding	Leaf-spring padding
Ironer cover	ARAMID needle-felt cloth
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Max. ironing performance at 25 % residual moisture in kg/h	87,0
Max. ironing performance at 50 % residual moisture in kg/h	51,0
Tested operating hours	20000
Control system	20000
Control system	Touch display
Touch display (optional)	Touch-Display PRI
Programme setting	Setting of defined
Trogramme soung	programme parameters
Minimum ironing speed, controlled in m/min	1,2
Maximum ironing speed, controlled in m/min	4,6
Adjustable temperature	Infinitely variable
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 450V 50-60HZ
Electric heater rating in kW	18,50
Total connected load in kW	19,10
Fuse rating in A	35
Possible voltage variant 1	
Electrical connection	3 AC 440V 50-60HZ
Electric heater rating in kW	17,00
Total connected load in kW	18,30
Fuse rating in A	35
Dimensions and weight	
External dimensions, height in mm	1110
External dimensions, width in mm	2469
External dimensions, depth in mm	1377
External dimensions, gross height in mm	1388
External dimensions, gross width in mm	2576
External dimensions, gross depth in mm	1096
Net weight in kg	415
Gross weight in kg	492
Maximum floor load in N/m ²	4071
Emissions data	
Emission sound pressure level in the workplace	56 dB(A) re 20 μPa
Heat dissipation into the room in MJ/h	10,80
τισαι σιοοιραιιστητίο της τουπ ΙΠ ΙΝΙΙ/Π	10,00

With 25 % residual moisture – performance data according to DIN 11902: the achievable ironing performance depends on overall conditions such as, for example, the type of laundry and the experience of the operator.



PRI 318 [EL SOM LAM IB RF] Rotary ironer, electrically heated with leaf-spring padding, feed-in belts and return feed for marine applications.



EAN: 4002516367901 / Material number: 11607850 / Old Material Number: 53318106SOM

Features	
Patented EasyFold out-feed table	•
Outfeed table extension (optional)	•
HPC heater plate	•
Automatic finger guard	•
FlexControl footswitch	•
In-feed table with feed-in bands	•
Pick-off bands	•
Laundry box	•
Laundry return feed	•
Favourite programme	•
Incorrect feed recognition	•
Air suspension	•
Pause function	•
High contact pressure	•
Clean and wax heater plate indicator (op	•
Emergency switch-off	•
APRI 319 care set for the heater plate included in the scope of delivery	•
Machine-independent accessories	•
Connection options	
Peak load cut-out/energy management (optional)	•
Standards, test certificates and symbols	
VDE	•
CE	•
WEEE	•
VDE-EMC	•
Splash-proof IPX0	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•