

Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



- Drum volume 110 l, maximum load size 12.0 kg
- Top cleaning & consumption values innovative Miele technology
- Ideal operation thanks to colour touch display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and WiFi

EAN: 4002516391289 / Material number: 11682900 / Old Material Number: 51912007SOM

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in kg	12,0
Load ratio	1:9
Load in kg	12,0
Drum volume in l	110
Door opening [Ø] in mm	415
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Innovative suds container	•
Maintenance-free motor with frequency converter	•
Patented honeycomb drum 2.0	•
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in I/	6,20
kg	
Specific energy consumption for cold water connection in kWh/kg	0,14
Specific water consumption for hot water connection in I/kg	5,90
Specific energy consumption for hot water connection in kWh/kg	0,06
Water consumption with cold water connection in I	74,4
Water consumption for cold water connection in Mops standard 60 °C programme in I	142,2
Energy consumption with cold water connection in kW	1,68
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	2,50
Programme duration in minutes with cold water connection	49
Water consumption with hot water connection in I	70,8
Water consumption for hot water connection in Mops standard 60 °C programme in I	139,9
Energy consumption with hot water connection in kW	0,72
Energy consumption for hot water connection in Mops standard 60 °C programme in kWh	1,00
Programme duration in minutes with cold water and hot water connection	42
Water consumption in ECO programme with cold water connection in I	69,6
Energy consumption in ECO programme with cold water	1,20
Programme duration in minutes with cold water connection in ECO programme	34
Water consumption in ECO programme with hot water connection in I	68,4
Energy consumption in ECO programme with hot water	0,36



Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



EAN: 4002516391289 / Material number: 11682900 / Old Material Number: 51912007SOM

Programme duration in minutes with cold water and hot	31
water connection in ECO programme	
Programme running time in minutes for Mops standard 60 °C programme with cold water connection	54
Programme running time in minutes for Mops standard 60 °C programme with hot water connection	47
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	44
Residual moisture when processing cleaning cloths in %	25
Spin speed in rpm	1150
g factor	458
Tested operating hours	30000
Control system	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Option to enter weight prior to start of programme	•
Standard/target grp programmes	
Basic programmes	•
Dispensing	
Detergent drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 480V 60HZ
Heater rating in kW	9,80
Total connected load in kW	10,40
Fuse rating in A	16
Possible voltage variant 1	
Electrical connection	3 AC 440V 60HZ
Ū.	3 AC 440V 60HZ 8,20
Electrical connection	8,20
Electrical connection Heater rating in kW Total connected load in kW	
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A	8,20 8,80
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage	8,20 8,80 16
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A	8,20 8,80
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number]	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number]	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight External dimensions, height in mm	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70 1350
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight External dimensions, height in mm External dimensions, width in mm	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70 1350 799
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight External dimensions, height in mm External dimensions, width in mm	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70 1350 799 924
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight External dimensions, height in mm External dimensions, width in mm External dimensions, depth in mm External dimensions, gross height in mm	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70 1350 799 924 1475
Electrical connection Heater rating in kW Total connected load in kW Fuse rating in A Water connection/drainage Cold water [number] Hot water [number] Hard water (optional) [number] Dump valve Dimensions and weight External dimensions, height in mm External dimensions, width in mm	8,20 8,80 16 3 x 1/2" hose w/ 3/4" union 1x 1/2" hose w/ 3/4" th. union 2 x 1/2" w/ 3/4" union DN 70 1350 799 924



Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.

EAN: 4002516391289 / Material number: 11682900 / Old Material Number: 51912007SOM

Gross weight in kg Maximum floor load in N/m ²	<u>308</u>
Emissions data	4302
	65 dP(A) ro 20 uPo
Emission sound pressure level in the workplace	65 dB(A) re 20 μPa
Heat dissipation into the room in MJ/h	6,48
Features	
Patented pre-spin	•
Cloth reprocessing	•
3-dimensional imbalance monitoring	
Disinfection rinse	
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
Spring-in-spring system	•
Temperature monitoring	•
Special heater element	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Weighing plinth (optional)	•
Add laundry	•
Programme selection via colour frame	•
Emergency switch-off	•
Machine-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	91
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•
Capacities	
Respirator masks [number]	10
Helmets [number]	3
Overalls [number]	2
Over jackets [number]	3
Chemical protection suits [number]	
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down duvets [number]	
Down pillows [number]	2
Cloths, 22 g [number]	289
Cotton mops, 40 cm / 190 g [number]	64
Cotton mops, 50 cm / 220 g [number]	56
Microfibre mops, 40 cm / 120 g [number]	100
Microfibre mops, 50 cm / 170 g [number]	72
Mops, office, 100 g [quantity]	120
Mops, stairway, 150 g [quantity]	80



Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



EAN: 4002516391289 / Material number: 11682900 / Old Material Number: 51912007SOM

Standards, test certificates and symbols	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•

Complies with Machinery Directive 2006/42/EC