

CM 7550 CoffeePassion  
Countertop coffee machine  
with OneTouch for Two and AutoDescale for easy operation.



- Fully automatic descaling – AutoDescale
- Perfect results and intense coffee flavour – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Communication with the machine could not be easier – WiFi Conn@ct
- Creamy milk froth for coffee specialities – Cappuccinatore

EAN: 4002516393368 / Material number: 11685790 /  
Old Material Number: 29755020GBX

General information	
Model identifier	CM 7550 CoffeePassion
Manufacturer material number	11685790
EAN number	4002516393368
Construction type and design	
Freestanding bean-to-cup coffee machine	•
Colour	Obsidian black
Convenience features	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
DoubleShot	•
Programmable User profiles	10
Conical grinder to preserve the taste	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Display	CM Touch
CupSensor	•
BrilliantLight	•
Expert mode	•
Heated cup rest	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	500
Bean container capacity, total in g	500
Capacity of water container in l	2,2
Milk container capacity in l	0,7
Capacity of waste container in capsules	16
Drip tray capacity	0,8
Easily accessible containers	•
Time of day display	•
Date display	•
Programmable switch-on time	•
Programmable switch-off time	•
Programmable standby time	•
Clock buffer in h	150
Programmable settings	•

CM 7550 CoffeePassion  
Countertop coffee machine  
with OneTouch for Two and AutoDescalc for easy operation.



EAN: 4002516393368 / Material number: 11685790 /  
Old Material Number: 29755020GBX

Drink specialities	
Selectable beverage portion size in ml	25-250
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Caffè americano, single	•
Long black, single	•
Warm water, single	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
Coffee pot	•
Teapot	•
Cappuccino, double	•
Latte macchiato, double	•
Latte macchiato, single	•
Efficiency and sustainability	
Energy-saving eco-mode selectable	•
Power rating in standby mode in W	<=0,5
Power rating in networked standby in W	<=1,0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
Power rating in standby mode in W	<=0,5
Power rating in networked standby in W	<=1,0
Time until automatic switch to standby in min	20

CM 7550 CoffeePassion  
Countertop coffee machine  
with OneTouch for Two and AutoDescale for easy operation.



EAN: 4002516393368 / Material number: 11685790 /  
Old Material Number: 29755020GBX

Time until automatic switch to networked standby in min 20

## Cleaning and care

AutoDescale function	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•

## Safety

System lock	•
-------------	---

## Technical data

Height-adjustable serving spout in cm	16,0
Height-adjustable serving spout in cm	8,0
Appliance width in mm	311
Appliance height in mm	397
Appliance depth in mm	445
Total rated load in kW	1,45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Length of supply lead in m	1,2

## Accessories included

Milk container made of glass	•
Descaling cartridge	•
Cleaning tablets	•

## Available display languages

Available display languages via MultiLingua

☐☐☐☐☐☐☐☐, ☐  
☐, ☐☐☐☐☐☐, deutsch,  
dansk, english, english  
(AU), english (CA), english  
(GB), english (US), suomi,  
français, français (CA),  
français (FR), ελληνικά,  
italiano, ☐☐☐☐, ☐☐☐☐,  
hrvatski, bahasa malaysia,  
nederlands, norsk, polski,  
português, română,  
русский, svenska, srpski,  
slovenčina, slovensčina,  
español, čeština, türkçe,  
українська, magyar