

## PDR 922 [EL SOM]

Vented dryer, electrically heated with programmable M Touch Pro controls, for marine applications.



- Drum volume 400.00 l, load size 16.0 kg–22.0 kg
- Unique, gentle fabric care – honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516410805 / Material number: 11722710 / Old Material Number: 52922006SOM

<b>Construction type and version</b>	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	16,0
Load size with a load ratio of 1:18	22,0
Drum volume in l	400,00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for offshore use	•
Suitable for marine use	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour	22,30
Specific energy consumption in kWh/kg	0,50
Programme duration in min.	23
Service life in drying cycles	40000
<b>Control system</b>	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3 AC 480V 50/60HZ
Electric heater rating in kW	26,50
Total connected load in kW	27,50
Fuse rating in A	50
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 440V 50/60HZ
Heater rating in kW	22,50
Total connected load in kW	23,50
Fuse rating in A	50
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1400
External dimensions, width in mm	906
External dimensions, depth in mm	1162
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	1254
Net weight in kg	198,9
Gross weight in kg	213

## PDR 922 [EL SOM]

Vented dryer, electrically heated  
with programmable M Touch Pro controls, for marine applications.



EAN: 4002516410805 / Material number: 11722710 / Old Material Number: 52922006SOM

Maximum floor load in N/m <sup>2</sup>	2521
<b>Emissions data</b>	
Emission sound pressure level in the workplace	62 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2,60
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Respirator masks [number]	16
Overalls [number]	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Down duvets [number]	2
Down pillows [number]	4
Cloths, 22 g [number]	364
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73
Microfibre mops, 40 cm [number]	133
Microfibre mops, 50 cm [number]	94
Summer horse blankets [number]	3
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•