

PDR 928 [EL SOM]

Vented dryer, electrically heated with programmable M Touch Pro controls, for marine applications.



- Drum volume 500.00 l, load size 45 (20.0) lb (kg) – 62 (28.0) lb (kg)
- Unique, gentle fabric care – honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516410928 / Material number: 11722730 / Old Material Number: 52928008SOM

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	45 (20,0) lb (kg)
Load size with a load ratio of 1:18	62 (28,0) lb (kg)
Drum volume in l	500,00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Specific energy consumption in kWh/kg	0,51
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0,51
Programme duration in min.	24
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 480V 50/60HZ
Electric heater rating in kW	31,80
Total connected load in kW	33,00
Fuse rating in A	50
Possible voltage variant 1	
Electrical connection	3 AC 440V 50/60HZ
Heater rating in kW	27,00
Total connected load in kW	28,20
Fuse rating in A	50
Dimensions and weight	
External dimensions, height in mm	1640
External dimensions, width in mm	1206
External dimensions, depth in mm	1019
External dimensions, gross height in mm	1766
External dimensions, gross width in mm	1390
External dimensions, gross depth in mm	1108
Net weight in kg	243,3

PDR 928 [EL SOM]

Vented dryer, electrically heated
with programmable M Touch Pro controls, for marine applications.



EAN: 4002516410928 / Material number: 11722730 / Old Material Number: 52928008SOM

Gross weight in kg	258
Maximum floor loading in N	3044
Emissions data	
Emission sound pressure level in the workplace	58 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3,30
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	12
Overalls [number]	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Down duvets [number]	2
Down pillows [number]	5
Cloths, 22 g [number]	545
Cotton mops, 40 cm [number]	105
Cotton mops, 50 cm [number]	91
Microfibre mops, 40 cm [number]	167
Microfibre mops, 50 cm [number]	118
Summer horse blankets [number]	3
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•