

## PDR 944 [EL SOM]

Vented dryer, electrically heated with programmable M Touch Pro controls, for marine applications.



- Drum volume 800.00 l, load size 32.0 kg–44.0 kg
- Unique, gentle fabric care – honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516410942 / Material number: 11722760 / Old Material Number: 52944007SOM

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	32,0
Load size with a load ratio of 1:18	44,0
Drum volume in l	800,00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Maximum evaporation capacity in l/hour	37,20
Specific energy consumption in kWh/kg	0,52
Programme duration in min.	28
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 480V 50/60HZ
Electric heater rating in kW	42,40
Total connected load in kW	44,10
Fuse rating in A	63
Possible voltage variant 1	
Electrical connection	3 AC 440V 50/60HZ
Heater rating in kW	36,00
Total connected load in kW	37,70
Fuse rating in A	63
Dimensions and weight of dryer	
External dimensions, height in mm	1640
External dimensions, width in mm	1206
External dimensions, depth in mm	1385
External dimensions, gross height in mm	1766
External dimensions, gross width in mm	1390
External dimensions, gross depth in mm	1474
Net weight in kg	294,3
Gross weight in kg	312

## PDR 944 [EL SOM]

Vented dryer, electrically heated  
with programmable M Touch Pro controls, for marine applications.



EAN: 4002516410942 / Material number: 11722760 / Old Material Number: 52944007SOM

Maximum floor load in N/m <sup>2</sup>	3780
<b>Emissions data</b>	
Emission sound pressure level in the workplace	63 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	4,00
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Respirator masks [number]	16
Overalls [number]	6
Over jackets [number]	9
Synthetic duvets [number]	4
Synthetic pillows [number]	8
Down duvets [number]	4
Down pillows [number]	8
Cloths, 22 g [number]	727
Cotton mops, 40 cm [number]	168
Cotton mops, 50 cm [number]	145
Microfibre mops, 40 cm [number]	267
Microfibre mops, 50 cm [number]	188
Summer horse blankets [number]	5
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•