

KFNS 7785 D

Built-in fridge-freezer combination

FlexiLight 2.0, DynaCool, NoFrost and My Ice for individual convenience.



- Spacious drawer with moisture control – DailyFresh
- Ice cubes with My Ice with water container
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool

EAN: 4002516420781 / Material number: 11738340 / Old Material Number: 38778501AUS

| | |
|--|----------------|
| Appliance category | |
| Fridge-freezer | • |
| Construction type | |
| Built-in appliance | • |
| Integrated appliance | • |
| Door hinge | right |
| Convertible door hinging | • |
| Side-by-side enabled | • |
| Design | |
| Refrigeration section lighting | FlexiLight 2,0 |
| Freezer compartment lighting | LED |
| Fan lighting | • |
| IceMaker lighting | • |
| User convenience | |
| Networking with Miele@home | • |
| Freshness system | DailyFresh |
| Fine adjustment inner door | • |
| ComfortClean | • |
| DynaCool | • |
| NoFrost | • |
| DuplexCool | • |
| ComfortSize | • |
| VarioRoom | • |
| SoftClose | • |
| Ice cube maker with water container (Mylce) | • |
| Control system | |
| Operating concept | FreshTouch |
| Fridge compartment can be switched off | Yes |
| Independent temperature regulation of fridge and freezer zones | Yes |
| Automatic SuperCool | • |
| SuperFreeze | • |
| No. of temperature zones | 2 |
| Sabbath mode | • |
| Party mode | • |
| Holiday mode | • |
| Fridge/Fridge section | |
| No. of shelves | 4 |
| of which illuminated | 2 |
| No. of crisper drawers | 1 |
| Dry back wall | CleanSteel |
| FlexiTray | • |
| Number of inner door racks for tinned food | 3 |
| Door rack for bottles | 1 |
| Door shelves | 4 |
| Freezer/Freezer section | |
| Number of freezer drawers | 3 |
| of which on runners | 2 |
| Safety | |
| Lock function | • |

KFNS 7785 D

Built-in fridge-freezer combination

FlexiLight 2.0, DynaCool, NoFrost and My Ice for individual convenience.



EAN: 4002516420781 / Material number: 11738340 / Old Material Number: 38778501AUS

| | |
|--|------------|
| Acoustic door alarm | • |
| Acoustic temperature alarm | • |
| Optical door alarm | • |
| Optical temperature alarm | • |
| Power cut indication for freezer section | • |
| Technical data | |
| Niche width in mm min. | 560 |
| Niche width in mm max. | 570 |
| Niche height in mm min. | 1772 |
| Niche height in mm max. | 1788 |
| Niche depth in mm | 550 |
| Appliance width in mm | 559 |
| Appliance height in mm | 1770 |
| Appliance depth in mm | 546 |
| Weight in kg | 75,5 |
| Door hinge technology | Fixed door |
| Max. door front weight – refrigerator, in kg | 18 |
| Max. door front weight – freezer, in kg | 12 |
| Climate class | SN-T |
| Total usable capacity in l | 243 |
| Current consumption (mA) | 1400 |
| Voltage in V | 220-240 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Frequency in Hz | 50-60 |
| Length of supply lead in m | 2,2 |
| Replacing lamps | Service |
| Accessories included | |
| Egg tray | • |