

PFD 104 SCVi XXL [MAR]

Fully integrated XXL dishwasher with 3D MultiFlex tray with baskets, approved by Lloyd's Register.



- Wash performance: 14 place settings in just 36 min^{*}
- 13 % less energy consumption^{**}
- Door opens automatically after two knocks – Knock2open
- Door closes on its own – AutoClose
- Innovative design and maximum convenience – 3D MultiFlex tray

^{*} Depending on site conditions (temperature of incoming water / power connection) values given may vary.

^{**} Based on the ECO programme, compared to predecessor.

EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

| Construction type and version | |
|--|-----------------------------|
| Construction type | Fully integrated dishwasher |
| XXL dishwashers | • |
| Range | ProfiLine |
| Wash system | Fresh water front loader |
| Number of levels | 2 |
| Front | Without front |
| Side panels | Galvanised |
| Fascia color | Obsidian black |
| Application | |
| Suitable for offshore and marine services | • |
| Performance data | |
| Tested virucidal efficacy | • |
| Proven hygiene | • |
| Shortest programme duration in min. | 36 |
| Maximum final rinse temperature in °C | 75 |
| Cleaning performance, place settings/cycle | 14 |
| Service life in wash cycles | 12500 |
| Control system | |
| Control system | Electronic controls |
| Programme selection | Programme selector buttons |
| Max. delay start in h | 24 |
| Time left display | • |
| Dishwashing programmes [number] | 8 |
| Programme sequence indicator | • |
| Choice of display language | • |
| Check filter indicator | • |
| Standard electrical connection | |
| Electrical connection | 3N AC 400V 50HZ |
| Heater rating in kW | 7,10 |
| Total connected load in kW | 7,30 |
| Fuse rating in A | 16 |
| Length of mains connection cable in m | 1,70 |
| Possible voltage variant 1 | |
| Electrical connection | AC 230V 50HZ |
| Heater rating in kW | 1,90 |
| Total connected load in kW | 2,10 |
| Fuse rating in A | 10-16 |
| Water connection/drainage | |
| Cold or hot water [number] | 1 |
| Required flow pressure in bar | 1,00-10,00 |
| Drain pump [DN] | 22 |
| Drain pump head height from floor level, max. in c | 100 |
| Integrated water softener | • |
| Maximum water hardness in mmol/l | 6,50 |
| Water protection system | Waterproof system |
| Length of water drain hose in cm | 150 |
| Dimensions and weight | |
| External dimensions, height in mm | 845 |

PFD 104 SCVi XXL [MAR]

Fully integrated XXL dishwasher with 3D MultiFlex tray with baskets, approved by Lloyd's Register.



EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

| | |
|---|--|
| External dimensions, net width in mm | 598 |
| External dimensions, net depth in mm | 550 |
| External dimensions, gross height in mm | 970 |
| External dimensions, gross width in mm | 670 |
| External dimensions, gross depth in mm | 690 |
| Usable space in wash cabinet, height in mm | 580 |
| Usable space in wash cabinet, width in mm | 510 |
| Usable space in wash cabinet, depth of upper basket | 450 |
| Usable space in wash cabinet, depth of lower basket in mm | 450 |
| In-feed height above floor in mm | 210 |
| Required niche width in mm | 600 |
| Net weight [kg] | 48 |
| Gross weight in kg | 57 |
| Maximum floor load in N/m ² | 1000 |
| Emissions data | |
| Emissions – sound pressure at workplace | 33 dB(A) re 20 µPa |
| Sound power (LwA) in dB(A) re 1 pW | 45,0 |
| Programmes | |
| Universal | • |
| Short | • |
| Hygiene | • |
| Cold/Pre-wash | • |
| Glasses | • |
| Plastics | • |
| Energy save/Eco | • |
| Intensive | • |
| Basket design | |
| MaxiComfort P baskets | • |
| Flexible FlexLine basket design | • |
| FlexCare glass holder [number] | 4 |
| FlexCare cup rack [number] | 2 |
| Height-adjustable upper basket | • |
| Patented 3D MultiFlex tray | • |
| Features | |
| Drying | Extra drying, Active condensation drying |
| 1 combi dispenser in the door for powder cleaning agent and rinsing agent | • |
| Wash cabinet made from high-quality stainless steel | • |
| BrilliantLight | • |
| AutoClose | • |
| EcoFeedback | • |
| Brilliant GlassCare | • |
| Adjustable final rinse temperature | • |
| Optical interface | • |
| SmartStart | • |
| FlexiTimer with EcoStart | • |
| WiFi module | • |
| Standards, test certificates and symbols | |
| CE | • |
| Complies with Machinery Directive 2006/42/EC | • |

PFD 104 SCVi XXL [MAR]
Fully integrated XXL dishwasher with 3D MultiFlex tray
with baskets, approved by Lloyd's Register.



EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

| | |
|----------------------|---|
| VDE | • |
| EMC radio suppressed | • |
| DIN EN 17735 | • |
| EN 1717 | • |
| Lloyd's Register | • |