

PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.

EAN: 4002516431169 / Material number: 11772780 /
Old Material Number: 52830306USA

Construction type and version	
Construction type	SlimLine
Range	Professional
Front	Iron grey
Load in kg	15,0
Load size with a load ratio of 1:25	12,0
Load size with a load ratio of 1:20	15,0
Drum volume in l	300,00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Performance data	
Maximum evaporation capacity in l/hour	11,50
Specific energy consumption in kWh/kg	0,59
Programme duration in min.	33
Control system	
Control system	Profitronic B Plus
Programmability	Setting of defined parameters
User interface	Residual moisture controlled
Time left display	•
Programme sequence indicator	•
Fascia panel with plain text	•
Selectable display languages	•
Standard/target grp programmes	
Basic programmes	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 220-240V 60HZ
Electric heater rating in kW	14,70
Total connected load in kW	13,10-15,40
Fuse rating in A	40
Possible voltage variant 1	
Electrical connection	3 AC 208V 60HZ
Heater rating in kW	11,00

- Drum volume 300.00 l, load size 15.0 kg
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Precision drying of all fabrics – PerfectDry

PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.

EAN: 4002516431169 / Material number: 11772780 /

Old Material Number: 52830306USA

Total connected load in kW	11,70
Fuse rating in A	35
Possible voltage variant 2	
Electrical connection	2 AC 208V 60HZ
Heater rating in kW	7,40
Total connected load in kW	8,10
Fuse rating in A	40
Dimensions and weight of dryer	
External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1089
External dimensions, gross height in mm	1810
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	139,0
Gross weight in kg	159
Maximum floor load in N	1584
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,70
Features	
Intelligent drum reversal	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Retractable plinth	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Standards, test certificates and symbols	
Complies with Machinery Directive 2006/42/EC	•