

G 7110 SC Front AutoDos  
Freestanding dishwashers  
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Fresh water dishwashers – from ?? in the Automatic programme
- Very easy door opening and closing – ComfortClose

EAN: 4002516435495 / Material number: 11780620 / Old Material Number: 21711018AE

<b>Model</b>	
Freestanding dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	CleanSteel front
Control panel version	Straight fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	44
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
<b>Efficiency and sustainability</b>	
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
<b>Wash programmes</b>	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
PowerWash	•
Gentle	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
<b>Dishwashing options</b>	
AutoDos	•
Express	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray
FlexCare cup rack	1
Basket design	ComfortPlus

G 7110 SC Front AutoDos  
Freestanding dishwashers  
with automatic dispensing thanks to AutoDos with integrated PowerDisk.




EAN: 4002516435495 / Material number: 11780620 / Old Material Number: 21711018AE

Safety	
Waterproof system	•
Filter indicator light	•
Safety lock	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119,5
Net weight in kg	57,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Energy stars	5,0
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, deutsch, english (AU), english (GB),
Accessories included	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

## G 7110 SC Front AutoDos

Freestanding dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, free standing dishwasher, 60cm (installation drawing)