

APCL 096
Laundry tub, red
with 85 l capacity.



- Suitable for FG 85
- Height (incl. handles) 34.5, width 80, depth 54 cm

EAN: 4002516474173 / Material number: 11824340 / Old Material Number: 59590096D

Product classification	
Washing machines	•
Tumble dryers	•
Ironers	•
Ironing systems	•
Machine/accessory category	
HM 16-80	•
HM 16-83	•
PM 1210	•
PM 1214	•
PM 1217	•
PM 1318	•
PM 1418	•
PM 1421	•
PRI 318	•
PRI 418	•
PRI 210	•
PRI 214	•
PRI 217	•
D 500-1750	•
D 500-2000	•
D 500-2200	•
D 500-2500	•
D 500-3000	•
D 500-3300	•
D 600-1750	•
D 600-2000	•
D 600-2200	•
D 600-2500	•
D 600-3000	•
D 600-3300	•
D 800-1300	•
D 800-1750	•
D 800-2000	•
D 800-2200	•
D 800-2500	•
D 800-3000	•
D 800-3300	•
M 500-1750	•
M 500-2000	•
M 500-2200	•
M 500-2500	•
M 500-3000	•
M 500-3300	•
PM 1621	•
PM 1625	•
PM 1630	•
PM 1635	•
PM 1825	•
PM 1830	•

APCL 096
Laundry tub, red
with 85 l capacity.



EAN: 4002516474173 / Material number: 11824340 / Old Material Number: 59590096D

PM 1835	•
PT 5135 C	•
PT 5136	•
PT 5137 WP	•
PT 5140 WP	•
PT 5141 WP	•
PT 5145 C	•
PT 5155 C	•
PT 5156	•
PT 5157 WP	•
PT 5186	•
PT 7186	•
PT 7188	•
PT 7135 C	•
PT 7136	•
PT 7137 WP	•
PT 7138	•
PT 8203	•
PT 8251	•
PT 8251 COP	•
PT 8253	•
PT 8257	•
PT 8257 WP	•
PT 8301	•
PT 8301 COP	•
PT 8303	•
PT 8331	•
PT 8331 COP	•
PT 8333	•
PT 8333 HW	•
PT 8337	•
PT 8337 HW	•
PT 8337 WP	•
PT 8401	•
PT 8403	•
PT 8403 HW	•
PT 8407	•
PT 8407 HW	•
PT 8503	•
PT 8503 HW	•
PT 8507	•
PT 8507 HW	•
PT 8803	•
PT 8803 HW	•
PT 8807	•
PT 8807 HW	•
PT 9136	•
PT 9137 WP	•
PW 413	•
PW 413 Mop Star 130	•
PW 418	•

APCL 096
Laundry tub, red
with 85 l capacity.

EAN: 4002516474173 / Material number: 11824340 / Old Material Number: 59590096D

PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 5134 MOPSTAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PW 9055	•
PW 9065	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PW 200 Profi@Work	•
PT 200 Profi@Work	•
PDR 300 SmartBiz	•
PWM 300 SmartBiz	•
PDR 500-08	•
PDR 507	•

APCL 096
Laundry tub, red
with 85 l capacity.



EAN: 4002516474173 / Material number: 11824340 / Old Material Number: 59590096D

PDR 900-08	•
PDR 908	•
PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
PDR 510	•
PDR 910	•
PDR 514	•
PDR 914	•
PDR 518	•
PDR 918	•
PDR 522	•
PDR 922	•
PDR 528	•
PDR 928	•
PDR 544	•
PDR 944	•
PIB 100	•
Product category	
Storage/transport system	•
Product properties	
Material	Plastic
Colour	Red
Volume in l	85
Dimensions and weight	
External dimensions, net height in mm	780
External dimensions, net width in mm	550
External dimensions, net depth in mm	290
External dimensions, gross height in mm	370
External dimensions, gross width in mm	590
External dimensions, gross depth in mm	1010
Net weight [kg]	2,91
Gross weight in kg	5,13