


DAS 4920
Slimline cooker hood
with EasySwitch controls for convenient operation



- Classic design – stainless steel panel, 90 cm wide
- Unique user convenience – Con@ctivity
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless-steel grease filter
- Recirculation mode – Active AirClean or Longlife AirClean filter

EAN: 4002516496038 / Material number: 11862230 / Old Material Number: 28S4920SD

Construction type	
Slimline cooker hood	•
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKFS 31-P, DKFS 31-R
Design	
Colour	Stainless steel
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Touch-on-glass controls	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A+++
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	22,9
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	1
Lighting	
LED	•
Number x W	1 x 3 W
Light intensity in lx	300 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	180
Air throughput in Level 2 (m ³ /h) according to EN 61591	280
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level (m ³ /h) according to EN 61591	600
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	37,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	47,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	55,0

DAS 4920
Slimline cooker hood
with EasySwitch controls for convenient operation



EAN: 4002516496038 / Material number: 11862230 / Old Material Number: 28S4920SD

Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	66,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	24,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	33,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	41,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	56,0
Recirculation	
Air throughput in Level 1 (m³/h) according to EN 61591	165
Air throughput in Level 2 (m³/h) according to EN 61591	265
Air throughput in Level 3 (m³/h) according to EN 61591	380
Air throughput in Booster level 1 (m³/h) according to EN 61591	585
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	43,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	61,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	73,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	29,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	59,0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	896
Canopy height in mm	36
Canopy depth in mm	273
Minimum height above electric hobs in mm	450
Net weight in kg	14,0
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0,09
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Diameter of exhaust duct in mm	150



DAS 4920
Slimline cooker hood
with EasySwitch controls for convenient operation



EAN: 4002516496038 / Material number: 11862230 / Old Material Number: 28S4920SD

Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein

DAS 4920
Slimline cooker hood
with EasySwitch controls for convenient operation



DAS2920, DAS2920EXTA, DAS2922Living, DAS4920,
Installation drawings

1) The front section of the wall unit must be fitted with a base panel to secure the cooker hood. If the appliance is fitted further back, e.g. to accommodate a front panel, then the shelf depth should be deeper accordingly. , 2) If a partition wall is to be provided in the unit, it must be removable., 3) Extraction, recirculation with conversion kit DUU 150., 4) Mounting is also possible in a 600 mm wide cabinet., * In this installation situation, the deflector plate is flush with the front edge of the housing unit carcass. , If you wish to position the cooker hood further forward or further back (e.g. because it has a front panel), dimensions have to be adapted accordingly., , Extraction: the height of the wall unit and the cut-out dimensions must take into account any accessories fitted, e.g. silencer, recirculation hood conversion kit).