

TWF760WP EcoSpeed&8kg

T1 heat-pump dryer:

with A+++ and DryCare 40 for efficient yet gentle drying.



- DryCare 40 – dries almost anything that can be washed at 40 °C
- Faster drying combined with maximum energy efficiency – EcoSpeed
- Quickly switch between 2 favourite fragrances – FragranceDos²
- Savings for the life of your tumble dryer – EcoDry technology
- Miele@home – clever networking opens up new possibilities*

* Additional digital offer from Miele & Cie. KG. All smart applications are made possible with the Miele@home system. The range of functions can vary depending on the model and the country.

EAN: 4002516476320 / Material number: 11871870 / Old Material Number: 12WF7602GB

Construction type	
Suitable for stacking	•
Side-by-side	•
Slot-in	•
Door hinge	left, Reversible
Convertible door hinging	•
Model	
Product brand	T1 White Edition
Heat pump dryer	•
Design	
Appliance colour	Lotus white
Control panel colour	Lotus white
Door design	Obsidian black with chrome ring
Rotary selector colour	Lotus White / Chrome ring
Control panel version	5° inclined
Control type	Rotary control
Display	DirectSensor white, 7 segment
Drying results	
PerfectDry precision drying	•
FragranceDos ² fragrance system	•
Intelligent drum reversal	•
Proven hygiene	•
Proven virus hygiene	•
Gentle laundry care	
Honeycomb drum	•
Load in kg	8,0
User convenience	
Networking with Miele@home	•
Wash2Dry	•
Delay start up to 24 hours	•
Time left display	•
Programme sequence indicator	No
Drum lighting	LED
Condensate container	•
Integrated condensed water drainage	•
AddLoad	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A+++
Annual energy consumption in kWh	161
Duration in minutes in the standard programme	165
Noise in the Cottons programme with full load in db(A) re 1 pW	66
Condensation efficiency class	A
Energy consumption in kWh in the Cottons Normal dry standard programme with a full load	1,32
EcoDry technology	•
Maintenance-free heat exchanger	•
ProfiEco motor	•
EcoSpeed	•

TWF760WP EcoSpeed&8kg

T1 heat-pump dryer:

with A+++ and DryCare 40 for efficient yet gentle drying.



EAN: 4002516476320 / Material number: 11871870 / Old Material Number: 12WF7602GB

Drying programmes

Cottons (coloureds)
Minimum iron
Delicates
Shirts
Woollens handcare
Express
Proofing
Bed linen
Warm air/DryFresh

•
•
•
•
•
•
•
•
•

Extras

Anti-crease
Buzzer
DryCare 40

•
•
•

Quality

Soft ribs

•

Safety

PIN-Code
Empty out container indicator
Clean filter indication
Optical interface

•
•
•
•

Technical data

Dimensions in mm (width)
Dimensions in mm (height)
Dimensions in mm (depth)
Appliance depth in mm with opened door
Weight in kg
Total rated load in kW
Voltage in V
Fuse rating in A
Frequency in Hz
Length of supply lead in m
Hermetically sealed
Type of coolant
Refrigerant quantity in kg
Refrigerant global warming potential in CO₂ e
Appliance global warming potential in CO₂ e
Replacing lamps

596
850
643
1077
56
1,10
220-240
13
50
2,0
•
R290
0,14
3
0,42
Customer Service

Accessories supplied


Fragrance flacon
Voucher for a second fragrance flacon

•
•


TWF760WP EcoSpeed&8kg

T1 heat-pump dryer:


with A+++ and DryCare 40 for efficient yet gentle drying.




T1 installation drawing, facia 5 degree, measures in mm



T1 drawing, facia 5 degree, measures in mm



T1 drawing, facia 5 degree, with porthole, measures in mm



T1 drawing, facia 5 degree, measures in mm