

APWM 073

Dispensing adapter installation kit

for connecting dispensing pumps directly, \varnothing 6 mm, max. capacity 9 kg.



- Suitable for hoses with 6 mm diameters
- For 9 kg Benchmark washing machines
- For 6 dispensing connections

EAN: 4002516589921 / Material number: 11902700 / Old Material Number: 59510073EU

| | |
|---|---------|
| Product category | |
| Washing machines | • |
| Machine/accessory category | |
| PWM 509 | • |
| PWM 909 | • |
| Product category | |
| Dispenser system | • |
| Product properties | |
| Material | Plastic |
| Colour | White |
| Dimensions and weight | |
| External dimensions, net height in mm | 0 |
| External dimensions, net width in mm | 0 |
| External dimensions, net depth in mm | 0 |
| External dimensions, gross height in mm | 12 |
| External dimensions, gross width in mm | 100 |
| External dimensions, gross depth in mm | 150 |
| Net weight [kg] | 0,08 |
| Gross weight in kg | 0,09 |