

B 4847 FashionMaster
Steam ironing system
with display and steamer for perfect ironing results and convenience.



- Uniform steam distribution – Miele honeycomb soleplate
- Professional results thanks to 4.0 bar steam pressure
- Convenient and easy to set up/store – 1-2 lift system
- Top-class ironing results thanks to active ironing board
- Convenient smoothing of hanging textiles – Steamer

EAN: 4002516527220 / Material number: 11978160 / Old Material Number: 13484721AS1

General information	
Model identifier	B 4847 FashionMaster
Manufacturer material number	11978160
EAN number	4002516527220
Design	
Iron colour	Anthracite/lotus white
Ironing board cover colour	Tayberry red
Display	1-line text display
Perfect ironing results	
Honeycomb soleplate	•
Steam pressure in bar	4,0
Steam quantity in g/min	100
Vertical steam	•
Steam starting from temperature level	2
Steam burst	•
Continuous steam	•
Steamer	•
Active ironing table (inflation and suction function)	•
Suction function	•
2-stage fan	•
Non-stick soleplate	•
Proven virus hygiene	•
Time-saving ironing	
Water container volume in l	1,25
Removable water container	•
Permanently refillable water container	•
Multi-layer ironing	•
User convenience	
All-in-one	•
1-2 Lift system	•
Variable height adjustment with gas pressure stay, in mm	830-1020
Castors gentle on the floor	•
Ironing board with Comfort Zone	•
Fan safety switch-on/switch-off	•
Fan memory function	•
Choice of language	•
Guided first-time use	•
Guided descaling	•
Automatic descaling	•
Automatic rinsing	•
Storage compartment for iron	•
Storage compartment for mains cable and accessories	•
Safety	
CoolDown function	•
AutoOff function	•
Technical data	
Dimensions in mm (width)	470
Dimensions in mm (height)	970

B 4847 FashionMaster
 Steam ironing system
 with display and steamer for perfect ironing results and convenience.



EAN: 4002516527220 / Material number: 11978160 / Old Material Number: 13484721AS1

Dimensions in mm (depth)	1480
Dimensions in mm (width), folded	470
Dimensions in mm (height), folded	1280
Dimensions in mm (depth), folded	370
Frequency in Hz	50-60

Accessories included	
Non-stick soleplate	•
Steamer	•
Premium ironing table cover	•
Steam hose holder	•
Test strips for determining water hardness	•
Descaling tablets	•

Available display languages

Available display languages via MultiLingua

, , deutsch,
 dansk, english (AU),
 english (GB), english (US),
 suomi, français, ελληνικά,
 italiano, , ,
 hrvatski, bahasa malaysia,
 nederlands, norsk, polski,
 portugûês, română,
 русский, svenska, srpski,
 slovenčina, slovenščina,
 español, čeština, türkçe,
 українська, magyar