

Complete C3 Parquet XL  
Cylinder vacuum cleaner  
with comprehensive accessories for nearly every cleaning challenge.



- Gentle on delicate hard floors – flexible Parquet Twister XL
- Retains even the smallest particles – AirClean+ filter
- Easy cleaning of larger areas thanks to 12 m operating radius
- Power Efficiency Motor with improved efficiency
- Convenient and versatile with three integrated accessories

EAN: 4002516555032 / Material number: 12032230 / Old Material Number: 41GSF532GB

|  |                              |
|--|------------------------------|
| <b>Construction type</b>                   |                              |
| Cylinder vacuum cleaner with dustbag       | •                            |
| Product brand                              | Complete C3                  |
| Motor type                                 | PowerLine                    |
| Product type                               | SGSF5                        |
| <b>Construction type and design</b>        |                              |
| Colour                                     | Obsidian black               |
| <b>User convenience</b>                    |                              |
| Electronic suction power control           | +/- footswitches             |
| Illuminated power indicator                | •                            |
| Ergonomic carrying handle                  | •                            |
| Ergonomic handle                           | •                            |
| Silence system                             | •                            |
| Suction tube                               | Comfort telescopic tube      |
| Park system for pauses during vacuuming    | •                            |
| Park system                                | on both sides                |
| Comfort cable rewind                       | •                            |
| <b>Mobility</b>                            |                              |
| Castors with steel shaft, gentle on floors | •                            |
| Dynamic Drive                              | •                            |
| Operating radius in m                      | 12                           |
| Cable length in m                          | 8,5                          |
| <b>Filter system</b>                       |                              |
| Vacuum cleaner bag type                    | HyClean GN                   |
| Dustbag volume in l                        | 4,5                          |
| Dustbag change indicator                   | •                            |
| Exhaust filter                             | AirClean Plus filter         |
| Motor protection filter                    | •                            |
| <b>Safety</b>                              |                              |
| Locking system for floorhead and handle    | •                            |
| Automatic dustbag positioning              | •                            |
| All-round furniture protection strip       | •                            |
| <b>Technical data</b>                      |                              |
| Power                                      | 890                          |
| Volume in dB                               | 78,0                         |
| Width in mm                                | 496                          |
| Height in mm                               | 227                          |
| Weight in kg                               | 7,3                          |
| Nominal rating in W                        | 890                          |
| <b>Accessories included</b>                |                              |
| Three-piece accessory set                  | Integrated                   |
| Upholstery nozzle                          | •                            |
| Crevice nozzle                             | •                            |
| Dusting brush with synthetic bristles      | •                            |
| Floorbrush                                 | SBB 400-3 Parquet Twister XL |
| SBD 365-3 floorhead                        | •                            |
| Parquet brush Twister XL SBB 400-3         | •                            |
| Filter                                     | AirClean Plus filter         |
| Cleaning tool                              | No                           |