

PUR 98 D

Island cooker hood

with energy-efficient LED lighting and light-touch switches for easy use.



- Timeless design – stainless steel canopy 898 mm wide
- Powerful – 650 m³/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation

EAN: 4002516585794 / Material number: 12050650 / Old Material Number: 28410858GB

Construction type	
Island cooker hood	•
Operating modes	
Type of air guide	Can be retrofitted
Design	
Colour	Stainless steel
User convenience	
Electronic controls	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A
Annual energy consumption in kWh/year	51,8
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	3
Lighting	
Number x W	4 x 3 W
Light intensity in lx	500 lx
Colour temperature in K	3000 Kelvin
Fan	
Dual-action fan	•
AC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	280
Air throughput in Level 2 (m ³ /h) according to EN 61591	330
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level (m ³ /h) according to EN 61591	650
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	48,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	57,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	69,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	31,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	35,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	51,0
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	190
Air throughput in Level 2 (m ³ /h) according to EN 61591	270
Air throughput in Level 3 (m ³ /h) according to EN 61591	330
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	460

PUR 98 D

Island cooker hood

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516585794 / Material number: 12050650 / Old Material Number: 28410858GB

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	57,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	62,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	66,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	73,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	40,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	45,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	49,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	56,0
Safety	
Safety switch-off	•
Technical data	
Overall height for vented and external in in. (mm)	690
Canopy width in mm	898
Overall height for extraction mode and external mode cooker hoods in mm	990
Canopy height in mm	70
Overall height for recirculation in in. (mm)	750
Canopy depth in mm	598
Overall height for recirculation mode cooker hoods in mm	1060
Minimum height above electric hobs in mm	450
Minimum height above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Net weight in kg	34,0
Length of supply lead in m	0,0
Hard-wired connection	•
Total rated load in kW	0,23
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein