

DGC 7250 CulinArt

Combination steam oven

for steam cooking, baking and roasting with networking and TasteControl.



- Clear text display with sensor controls – DirectSensor S
- Excellent results – MonoSteam technology
- Especially light dough and nicely browned crusts – Moisture plus
- Ensures your food won't overcook – TasteControl
- Easy to clean – PerfectClean finish

EAN: 4002516599135 / Material number: 12099500 / Old Material Number: 22725032D

General information	
Model identifier	DGC 7250 CulinArt
Manufacturer material number	12099500
EAN number	4002516599135
Construction type and design	
Colour	Graphite grey
VitroLine	•
Construction type and design	
Steam combination oven	•
Convenience features	
TasteControl	•
Rapid heat-up	•
External steam generation	•
Operating modes	
Fan plus	•
Conventional heat	•
Steam cooking	•
Moisture plus	•
Intensive bake	•
Auto roast	•
Fan grill	•
Grill	•
Grill operating modes	•
Bottom heat	•
Eco hot air	•
Defrost	•
Automatic programmes	•
User convenience	
Networking with Miele@home	•
Display	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Quantity-independent cooking	•
Timer functions	•
Time of day display	•
Minute minder	•
Programmable start of cooking duration	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
Individual settings	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A+
Automatic residual heat utilisation	•

DGC 7250 CulinArt

Combination steam oven

for steam cooking, baking and roasting with networking and TasteControl.



EAN: 4002516599135 / Material number: 12099500 / Old Material Number: 22725032D

Power rating in off mode in W	0,3
Power rating in standby mode in W	0,8
Power rating in networked standby in W	2,0
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
Time until automatic switch to off mode in min	20
Cleaning and care	
Enamelled oven compartment with PerfectClean finish and catalytic rear liner	•
External steam generator	•
Floor heater for condensate reduction	•
Maintenance programmes	•
Soak programme	•
Oven compartment drying programme	•
Removable stainless-steel side racks	•
Automatic descaling	•
CleanGlass door	•
Steam techn./water supply	
MonoSteam	•
Steam generator power in kW	2,20
Fresh water container volume in l	1,0
Suction tube for drawing in water	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Sensor lock	•
Technical data	
Oven compartment volume in l	76
No. of shelf levels	5
Appliance dimensions (W x H x D) in mm	595 x 596 x 568
Numbered shelf levels	•
Door hinge	Bottom
Oven light	1 halogen spot
Oven mode temperatures min. in °C	30
Oven mode temperatures max. in °C	250
Oven temperatures in °C	30–250
Steam-cooking mode temperatures min. in °C	70
Steam-cooking mode temperatures max. in °C	100
Steam oven temperatures in °C	70–100
Niche dimensions (W x H x D) in mm	560-568 x 590-595 x 550
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Appliance width in mm	595
Appliance height in mm	596
Appliance depth in mm	568

DGC 7250 CulinArt

Combination steam oven

for steam cooking, baking and roasting with networking and TasteControl.



EAN: 4002516599135 / Material number: 12099500 / Old Material Number: 22725032D

Weight in kg	42,0
Total rated load in kW	3,50
Voltage in V	220-240
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Mains cable with plug	•
Replacing lamps	Service
Accessories included	
Baking tray with PerfectClean HBB 71	1
Universal tray with PerfectClean HUBB 71	1
Baking and roasting rack with PerfectClean HBRR 71	1
PerfectClean FlexiClip runners HFC 71 (pair)	1
Removable side runners (pair)	1
Perforated stainless-steel cooking containers	1
Solid stainless steel cooking containers	1
Voucher for an induction compatible HUB 5001-M	1
Gourmet oven dish	
Descaling tablets	2
Available display languages	


Available display languages via MultiLingua

? ? ? ? ? ? ? , ? ? , ?
 ? ? ? , deutsch, dansk,
 english, suomi, français,
 ελληνικά, italiano, ? ? ? ,
 ? ? ? , hrvatski, bahasa
 malaysia, nederlands, norsk,
 polski, português, română,
 русский, svenska, srpski,
 slovenčina, slovenščina,
 español, čeština, türkçe,
 українська, magyar

DGC 7250 CulinArt


Combination steam oven

for steam cooking, baking and roasting with networking and TasteControl.




installation H7000 XL, installation drawing

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm²




side view H7000 XL, installation drawings

22 mm – glass, 23,3 mm – metal




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings

If the oven is to be installed under a hob, follow the instructions for installing the hob and the height of the hob.



H7000 handle, glass, installation drawings

1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 27 mm, 5) 32.5 mm



side view H7000 XL build-under, installation drawing

22 mm – glass, 23,3 mm – metal