

PFD 401 U [WB Marine]  
Built-under fresh-water dishwasher  
with baskets, approved by Lloyd's Register.



- Versatile processing of two wire or plastic baskets per cycle
- Max. cleaning performance\*: 228 plates/h or 12 baskets/h
- Excellent user convenience with touch display – M Touch Basic
- First-class results thanks to freshwater wash system
- Always the right programme – item-specific solutions

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516604648 / Material number: 12143280 / Old Material Number: 61040132MAR

<b>Construction type and version</b>	
Construction type	Built-under dishwasher
Range	MasterLine
Model	Marine applications
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Without lid
Side panels	Galvanised
<b>Application</b>	
Suitable for offshore and marine services	•
<b>Performance data</b>	
Tested virucidal efficacy	•
Proven hygiene	•
Circulation pump Qmax in l/min.	390
Shortest programme duration in min.	10
Maximum final rinse temperature in °C	70
Cleaning performance, plates/h	228
Cleaning performance, baskets/h	12
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	28000
<b>Miele MOVE</b>	
Network-enabled with Miele MOVE	•
Display of machine status and details	•
Receipt of push notifications	•
Assignment of individual machine names	•
Location configuration	•
Reorder consumables	•
Fault management	•
Operating data acquisition	•
Self-help function	•
Installation of remote updates and software updates	•
<b>Control system</b>	
Control system	M Touch Basic
Max. delay start in h	24
Time left display	•
Programmes [number]	10
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
<b>Standard electrical connection</b>	
Electrical connection	2 AC 208V 60HZ
Heater rating in kW	5,40
Total connected load in kW	5,80
Fuse rating in A	30
Length of mains connection cable in m	1,90
NEMA plug: Twist Lock L6-30	•
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 208V 60HZ
Heater rating in kW	5,40

PFD 401 U [WB Marine]  
 Built-under fresh-water dishwasher  
 with baskets, approved by Lloyd's Register.



EAN: 4002516604648 / Material number: 12143280 / Old Material Number: 61040132MAR

Total connected load in kW	5,80
Fuse rating in A	20
<b>Water connection/drainage</b>	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	0,40-10,00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	10,70
Water protection system	Waterproof system
Water consumption per wash cycle in l	17,50
Length of water inlet hose in cm	170
Length of water drain hose in cm	150
<b>Dimensions and weight</b>	
External dimensions, height in mm	820
External dimensions, net width in mm	598
External dimensions, net depth in mm	580
External dimensions, gross height in mm	920
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	740
Usable space in wash cabinet, height in mm	530
Usable space in wash cabinet, width in mm	536
Usable space in wash cabinet, depth of upper basket	474
Usable space in wash cabinet, depth of lower basket in mm	516
In-feed height above floor in mm	216
Required niche width in mm	600
Net weight [kg]	65
Gross weight in kg	75
Maximum floor load in N/m <sup>2</sup>	1200
<b>Emissions data</b>	
Emissions – sound pressure at workplace	47 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	59,0
Heat dissipation into the room in MJ/h	1,08
<b>Programmes</b>	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Beer glasses	•
Cutlery	•
Plastics	•
Intensive	•
Reactivation	•
Drainage	•
<b>Basket design</b>	
2 x E 816 inserts for plates	•
1 x APFD 215 upper basket	•
1 x APFD 220 lower basket for inserts	•
2 x APFD 420 insert for cutlery	•

PFD 401 U [WB Marine]  
 Built-under fresh-water dishwasher  
 with baskets, approved by Lloyd's Register.



EAN: 4002516604648 / Material number: 12143280 / Old Material Number: 61040132MAR

Height-adjustable upper basket	•
Combinable with APFD 210 bottle basket	•
<b>Features</b>	
Drying	without
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•
AutoClose	•
Perfect GlassCare	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Optical interface	•
Highly effective filter system with filter monitoring	•
WiFi module	•
A wide range of accessories (optional)	•
<b>Connection options</b>	
External dispensing module for liquid detergent	•
External dispensing module for rinse aid	•
<b>Standards, test certificates and symbols</b>	
Complies with Machinery Directive 2006/42/EC	•
Splash-protection IPX1	•
EMC radio suppressed	•
DIN 10512	•
DIN EN 17735	•
ETL	•
Lloyd's Register	•