

DOS G 80 comfort
Hose metering pump
with fill level indicator for automatic dispensing of liquid cleaning agents.

EAN: 4002516627944 / Material number: 12187270 / Old Material Number: 67747540D



- For canisters up to 325 mm tall (up to canister opening)
- Dispensing up to 55 Milliliter per minute
- Adjustable via the dishwasher controls
- Flexible cap (covers DIN 50 and 51 threads)
- Min. canister opening: 31 mm

Machine affiliation	
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
Product category	
External dispensing system	•
Product properties	
Material	Plastic
Colour	White
Production rate in ml/60 s	55
Length of suction lance in mm	352
Length of dispensing hose to suction lance in mm	1800
Length of dispensing hose from machine to dispensing module in mm	2850
Length of mains connection cable to machine in mm	2800
Minimum width of canister opening in mm	31
Maximum width of canister opening in mm	60
Standard electrical connection	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	200-230
Frequency in Hz	50
Total rated load in kW	0,01
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	114
External dimensions, net width in mm	115
External dimensions, net depth in mm	139
External dimensions, gross height in mm	155
External dimensions, gross width in mm	485
External dimensions, gross depth in mm	231
Net weight in kg	1,71
Gross weight in kg	3,64