

## KWT 2672 ViS

### MasterCool wine conditioning unit

For high-end design and technology on a large scale.



- Push2open for convenient door-opening assistance
- Serve and enjoy to perfection – incl. SommelierSet
- Various wines at the perfect temperature – 3 temperature zones
- Flexible storage of large wine bottles thanks to FlexiFrame
- Light floods the interior thanks to LED elements – BrilliantLight

EAN: 4002516654742 / Material number: 12253670 /  
Old Material Number: 36267205AUS

| General information                  |                |
|--------------------------------------|----------------|
| Model identifier                     | KWT 2672 ViS   |
| Manufacturer material number         | 12253670       |
| EAN number                           | 4002516654742  |
| Marketing class                      | Diamond        |
| Appliance category                   |                |
| Wine conditioning unit               | •              |
| Construction type                    |                |
| Built-in appliance                   | •              |
| Integrated appliance                 | •              |
| Door hinge                           | Left           |
| Convertible door hinging             | •              |
| Side-by-side enabled                 | •              |
| Design                               |                |
| Lighting                             | BrilliantLight |
| User convenience                     |                |
| Networking with Miele@home           | •              |
| Operating concept                    | MasterSensor   |
| Sabbath mode                         | •              |
| DynaCool                             | •              |
| SoftClose                            | •              |
| Push2open                            | •              |
| MaxLoad hinge                        | •              |
| FlexiFrame                           | •              |
| Number of FlexiFrame wooden racks    | 9              |
| Rack material                        | Beech          |
| SommelierSet                         | •              |
| NoteBoard                            | •              |
| Smart Extras                         |                |
| Wine Storage Guide                   | •              |
| Cooling modes                        | •              |
| Feature lighting                     | •              |
| Push notifications                   | •              |
| RemoteUpdate                         | •              |
| Smart Home Integration               | •              |
| Control system                       |                |
| No. of temperature zones             | 3              |
| Min. temperature setting range in °C | 5              |
| Max. temperature setting range in °C | 20             |
| Efficiency                           |                |
| Annual energy consumption in kWh     | 155,13         |
| Energy consumption in 24 h in kWh    | 0,42           |
| Safety                               |                |
| Lock function                        | •              |
| Acoustic door alarm                  | •              |
| Acoustic temperature alarm           | •              |
| Optical door alarm                   | •              |
| Optical temperature alarm            | •              |

## KWT 2672 ViS

### MasterCool wine conditioning unit

For high-end design and technology on a large scale.



EAN: 4002516654742 / Material number: 12253670 /

Old Material Number: 36267205AUS

| Technical data                                   |                  |
|--------------------------------------------------|------------------|
| Niche width in mm min.                           | 610              |
| Niche width in mm max.                           | 613              |
| Niche height in mm min.                          | 2134             |
| Niche height in mm max.                          | 2164             |
| Niche depth in mm                                | 629              |
| Appliance dimensions (W x H x D) in mm           | 603 x 2127 x 610 |
| Appliance width in mm                            | 603              |
| Appliance height in mm                           | 2127             |
| Appliance depth in mm                            | 610              |
| Weight in kg                                     | 147,0            |
| Door hinge technology                            | Fixed door       |
| Max. door front weight – refrigerator, in kg     | 73               |
| Climate range                                    | SN-T             |
| Refrigerator compartment in l                    | 370              |
| Total usable capacity in l                       | 370              |
| 0.75 l Bordeaux bottle capacity (no. of bottles) | 91 bottles       |
| Acoustic airborne noise emission class (A–D)     | D                |
| Sound emissions in dB(A) re 1 pW                 | 42               |
| Current consumption (mA)                         | 3000             |
| Voltage in V                                     | 220-240          |
| Fuse rating in A                                 | 10               |
| Number of phases                                 | 1                |
| Frequency in Hz                                  | 50               |
| Length of supply lead in m                       | 3,0              |

#### Available display languages


Available display languages via MultiLingua

[?][?][?][?][?][?][?], [?]  
 [?], [?][?][?][?], deutsch,  
 dansk, english, english  
 (AU), english (CA), english  
 (GB), english (US), eesti,  
 suomi, français, français  
 (CA), français (FR),  
 ελληνικά, italiano, [?][?]  
 [?], [?][?][?], hrvatski,  
 latviesu, lietuviu, bahasa  
 malaysia, nederlands, norsk,  
 polski, portuguese, română,  
 русский, svenska, srpski,  
 slovenčina, slovensčina,  
 español, čeština, türkçe,  
 українська, magyar

## KWT 2672 ViS


### MasterCool wine conditioning unit

For high-end design and technology on a large scale.




Opening angle 90°/115°, right side stop, MasterCool (Sketch) with footnote

A) Appliance door, K 2611 Vi, KWT 2611 Vi, KWT 2611 SF, KWT 2671 ViS: 677 mm (26 2/3 inch);, K 2612 Vi, KWT 2612 Vi, KWT 2612 SF, KWT 2672 ViS: 677 mm (26 2/3 inch);, K 2811 Vi, K 2811 SF, KF 2811 Vi, KF 2811 SF: 829 mm (32 2/3 inch);, K 2812 Vi, K 2812 SF, KF 2812 Vi, KF 2812 SF: 829 mm (32 2/3 inch);, K 2911 Vi, K 2911 SF, KF 2911 Vi, KF 2911 SF: 982 mm (38 2/3 inch);, K 2912 Vi, K 2912 SF, KF 2912 Vi, KF 2912 SF: 982 mm (38 2/3 inch);, B) Furniture front (max. 38 mm) (1 1/2 inch), C) Door handle, D) Distance from the door to the wall (without furniture front and door handle):, K 2611 Vi, KWT 2611 Vi, KWT 2611 SF, KWT 2671 ViS: 296 mm (11 2/3 inch);, K 2612 Vi, KWT 2612 Vi, KWT 2612 SF, KWT 2672 ViS: 296 mm (11 2/3 inch);, K 2811 Vi, K 2811 SF, KF 2811 Vi, KF 2811 SF: 363 mm (14 1/3 inch);, K 2812 Vi, K 2812 SF, KF 2812 Vi, KF 2812 SF: 363 mm (14 1/3 inch);, K 2911 Vi, K 2911 SF, KF 2911 Vi, KF 2911 SF: 428 mm (16 7/8 inch);, K 2912 Vi, K 2912 SF, KF 2912 Vi, KF 2912 SF: 428 mm (16 7/8 inch);, E) ONLY valid for SF versions: A + 25 mm (1 inch)




Side-by-side, MasterCool, without partition wall, with heating mat (Sketch) (with footnote)


1) Heating mat KSK 2001 (EU, AUS, CN) or KSK 2002 (US, CA, MX, BR)



KWT2611Vi, KWT2671ViS, KWT2601Vi, KWT2661ViS, installation, MasterCool, installation drawings




Sideview, MasterCool, Sketch



Side-by-Side, MasterCool, footnote, installation drawings

1. KSK 2001/2002, 2. Device A, 3. Device B, A = niche device A, B = niche device B




KFP2455ed/cs, KFP2454ed/cs, front panel, front dimensions, MasterCool, installation drawings

## KWT 2672 ViS


### MasterCool wine conditioning unit

For high-end design and technology on a large scale.



Installation, MasterCool, \*footnote, installation drawings

1. View from the front, 2. Mains connection cable, L = 3000 mm (118 inch), 3. No water/ELT connections permitted in this area



KWT2672ViS, KWT2662ViS, KWT2671 ViS, MasterCool, inner space, modeling, installation drawings