

H 7840 BMX

Handleless microwave combination oven

with a seamless design, automatic programmes and food probe



- Easy cleaning – compartment with PerfectClean & linen structure
- Network-enabled WiFi appliance – Miele@home
- Large touch display with movement sensor – M Touch + MotionReact
- Faster and more consistent results – Quick & Gentle
- Get what you want in one easy step – Quick MW and Popcorn button

EAN: 4002516713463 / Material number: 12310190 /

Old Material Number: 22784086GB

Construction type and design	
ArtLine	•
Handleless	•
Construction type and design	
Built-in microwave combination oven	•
User convenience	
3 in 1	Oven, Microwave, Oven with microwave function
Convenience features	
Quick & Gentle	•
Rapid heat-up	•
Pre-heating	•
Food probe	With cable
Keeping warm	•
Crisp function	•
Operating modes	
Fan plus	•
Conventional heat	•
Microwave	•
Microwave + Fan plus	•
Microwave + Grill	•
Microwave + Fan grill	•
Microwave with Auto roast	•
Intensive bake	•
Auto roast	•
Fan grill	•
Grill	•
Bottom heat	•
Low temperature cooking	•
Eco hot air	•
Defrosting	•
Automatic programmes	•
Country-specific automatic programmes	•
Special applications	•
Design	
Colour	Obsidian black matt
User convenience	
Networking with Miele@home	•
Display	M Touch
MotionReact proximity sensor	•
MotionReact: light comes on when movement is detected	•
MotionReact: display comes on when movement is detected	•
MotionReact: audible signal is acknowledged when movement is detected	•
MotionReact: detection of cabinet fronts	•
SoftOpen	•
Touch2Open	•

H 7840 BMX

Handleless microwave combination oven

with a seamless design, automatic programmes and food probe



EAN: 4002516713463 / Material number: 12310190 /

Old Material Number: 22784086GB

MultiLingua	•
MyMiele	•
Help function	•
Popcorn function	•
Polyphonic buzzers	•
Time of day display	•
Clock synchronisation	•
Date display	•
Minute minder	•
Programmable start of cooking duration	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
Suggestion microwave power	•
Quick microwave	•
User programmes	•
Individual settings	•
Efficiency and sustainability	
Power rating in off mode in W	0,3
Automatic residual heat utilisation	•
Power rating in standby mode in W	0,8
Time until automatic switch to standby in min	20
Time until automatic switch to off mode in min	20
Power rating in networked standby in W	2,0
Time until automatic switch to networked standby in min	20
Cleaning and care	
Stainless-steel oven compartment with linen structure and PerfectClean	•
Hinged grill element	•
CleanGlass door	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Sensor lock	•
Technical data	
Oven compartment volume in l	43
No. of shelf levels	3
Number of shelf levels oven compartment 1	3
Number of shelf levels oven compartment 2	3
Oven light	1 LED spot
Temperatures in °C	30–250
Temperatures min. in °C	30
Temperatures max. in °C	250
Electronically controlled microwave power	•
Microwave power levels in W	

H 7840 BMX

Handleless microwave combination oven

with a seamless design, automatic programmes and food probe



EAN: 4002516713463 / Material number: 12310190 /
Old Material Number: 22784086GB

Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	450
Niche height max. in mm	452
Niche depth in mm	550
Appliance width in mm	595
Appliance height in mm	456
Appliance depth in mm	562
Weight in kg	38,0
Total rated load in kW	3,20
Voltage in V	220-240
Length of supply lead in m	2,00
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Neutral conductor	Yes
Mains cable with plug	•
Replacing lamps	Service
Accessories included	
Baking and roasting rack with PerfectClean	1
Wired food probe	1
Glass tray	2


Available display languages

Available display languages via MultiLingua


bahasa malaysia, dansk,
deutsch, english, español,
français, hrvatski, italiano,
magyar, nederlands, norsk,
polski, portugês, русский,
română, slovenčina,
slovenščina, srpski, suomi,
svenska, türkçe, українська,
čeština, ελληνικό,
[?][?][?][?][?][?], [?][?], [?]
[?][?], [?][?][?][?], [?][?][?]

H 7840 BMX


Handleless microwave combination oven
with a seamless design, automatic programmes and food probe




side view H7000 BM, installation drawings, GB, AUS
22 mm – glass, 23.3 mm – metal




built-in H7000 BM, installation drawing




built-in H7000 BM build-under, installation drawings
If the oven is to be installed under a hob, follow the instructions for installing the hob and the height of the hob.




Installation H7000 BM, installation drawings, GB, AUS
1) Mains connection cable, L=2000 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm²




Installation H7000 BM XL, installation drawings



side view H7000 BM build-under, installation drawing, GB, AU
22 mm – glass, 23.3 mm – metal



Side view Kombi BM XL, installation drawings
22 mm – glass, 23.3 mm – metal



Installation Kombi BM XL, installation drawings
22 mm – glass, 23.3 mm – metal