

## PDW 909 [EL DP DD SOM]

Professional washer-dryer stack, electric heating, with drain pump for washing/drying in the smallest space, with drain pump, for marine use.



EAN: 4002516703082 / Material number: 12341250 / Old Material Number: 51909513SOM

Construction type and version	
Construction type	Front-loading stack
Range	Performance Plus
Front	Stainless steel
Washer-extractor load capacity in kg	9,0
Tumble dryer load capacity in kg	9,0
Washer-extractor fill ratio	1:9
Tumble dryer fill ratio	1:20
Washer-extractor drum volume in l	80
Tumble dryer drum volume in l	180
Drying system	Exhaust air
Washer-extractor door opening [Ø] in mm	370
Tumble dryer door opening [Ø] in mm	440
Door opening angle in degrees	180
Door hinge	Washing right/drying left
Automatic door lock	•
Honeycomb drum	•
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Specific washer-extractor energy consumption in kW	0,03
Residual moisture with cold rinse in %	47
Residual moisture with hot rinse in %	44
Washer-extractor spin speed in rpm.	1300
Washer-extractor g-factor	518
Control system	
Control type for washing machine	M Touch Pro Plus
Control type for tumble dryer	M Touch Pro
Programmability for washing machine	Frei Programmierbar
Programmability for tumble dryer	Programmierbar
Max. delay start in h for washing machine	Frei wählbar
Max. delay start in h for tumble dryer	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard/target grp programmes	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for laundrettes	•
Programmes for residential homes and apartments	•
Programmes for dry cleaners	•
Programmes for commercial laundries	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for universities, nurseries, and school	•
Programmes for hospitals	•
Programmes for camp sites	•
Programmes for sports clubs	•

## PDW 909 [EL DP DD SOM]

Professional washer-dryer stack, electric heating, with drain pump for washing/drying in the smallest space, with drain pump, for marine use.



EAN: 4002516703082 / Material number: 12341250 / Old Material Number: 51909513SOM

Programmes for beauty clinics, spas, and fitness studios	•
Programmes for domestic use	•
Programmes for doctors' and dentists' practices	•
<b>Washing machine dispensing</b>	
Detergent drawer	3 compartments
Maximum number of connections for liquid dispenser	6
Empty sensor	•
<b>Standard electrical connection</b>	
Type of heating washing machine	Electric
Type of heating tumble dryer	Electric
Electrical connection washing machine	3 AC 480/440/400 V 60 Hz
Heater rating washing machine in kW	7,20
Total connected load washing machine in kW	7,45
Electrical connection tumble dryer	3 AC 480/440/400 V 50/60 Hz
Heater rating tumble dryer in kW	6,14
<b>Possible voltage options</b>	
Electrical connection washing machine	3 AC 480/440/400 V 60 Hz
Heater rating washing machine in kW	7,20
Total connected load washing machine in kW	7,45
Fuse rating washing machine in A	16,0
Electrical connection tumble dryer	3 AC 480/440/400 V 50/60 Hz
Fuse rating tumble dryer in A	10,0
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Grey water (optional) [number]	1 x 1/2" w/ 3/4" union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, net height in mm	1940
External dimensions, net width in mm	692
External dimensions, net depth in mm	761
Net weight in kg	208,0
Gross weight in kg	232,0
Maximum floor load in N/m <sup>2</sup>	3235
Net weight in kg	139,00
<b>Emissions data</b>	
Emission sound pressure level in the workplace	63 dB(A) re 20 µPa
Washer-extractor heat output to the room in Mj/h	3,00
Tumble dryer heat output to the room in Mj/h	1,62
<b>Features</b>	
Washer-extractor disinfection rinse	•
Washer-extractor temperature monitoring	•
Volumetric flow meter, washer-extractor	•
Special heater element washing machine	•
Intelligent tumble dryer drum reversal	•
Axial air flow dryer	•
Extra-large tumble dryer filter	•

## PDW 909 [EL DP DD SOM]

Professional washer-dryer stack, electric heating, with drain pump for washing/drying in the smallest space, with drain pump, for marine use.



EAN: 4002516703082 / Material number: 12341250 / Old Material Number: 51909513SOM

PerfectDry tumble dryer	•
SoftLift tumble dryer drum ribs	•
Low temperature tumble dryer function	•
Drying basket (optional)	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN for washing machine	•
WiFi	•
Connector Box	•
<b>Capacities</b>	
Respirator masks [number]	13
Protective suits [number]	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down duvets [number]	1
Down pillows [number]	2
Cloths, 22 g [number]	204
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	33
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	2
<b>Standards, test certificates and symbols</b>	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•