

PUR 98 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



- Timeless design – matt black canopy 898 mm wide
- Powerful – 650 m³/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation

EAN: 4002516717706 / Material number: 12358160 / Old Material Number: 28419855D

General information	
Model identifier	PUR 98 W
Manufacturer material number	12358160
EAN number	4002516717706
Marketing class	Silver
Construction type	
Wall mounted cooker hood	•
Appliance type and design	
Appliance colour	Matt black
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
Active charcoal filter (order separately)	DKF 12-P, DKF12-R
Design	
Possible in RAL colour (specify colour code when ordering)	•
User convenience	
Electronic controls	•
Controls	Light-touch switches with LEDs
Power levels (number without Booster level)	3
Booster levels	1
Easy-to-clean canopy interior – CleanCover	•
Efficiency	
Energy efficiency class (A+++ – D)	A
Annual energy consumption in kWh/year	49,7
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	3
Lighting	
Number x W	3 x 3 W
Light intensity in lx	450 lx
Colour temperature in K	3000 Kelvin
Fan	
Dual-action blower	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	265
Air throughput in Level 2 (m ³ /h) according to EN 61591	320
Air throughput in Level 3 (m ³ /h) according to EN 61591	395
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	650
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	52,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	56,0

PUR 98 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



EAN: 4002516717706 / Material number: 12358160 / Old Material Number: 28419855D

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	67,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	41,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	52,0
Recirculation	
Air throughput in Level 1 (m³/h) according to EN 61591	190
Air throughput in Level 2 (m³/h) according to EN 61591	270
Air throughput in Level 3 (m³/h) according to EN 61591	330
Air throughput in Booster level 1 (m³/h) according to EN 61591	460
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	54,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	60,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	64,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	71,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	45,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	56,0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	898
Overall hood height for extraction mode and external in mm	685–1005
Overall height for recirculation mode cooker hoods in mm	815–1135
Overall height for vented and external in in. (mm)	685
Overall height for extraction mode and external mode cooker hoods in mm	1005
Canopy height in mm	62
Overall height for recirculation in in. (mm)	815
Canopy depth in mm	500
Overall height for recirculation mode cooker hoods in mm	1135
Net weight in kg	25,0
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum height above electric hobs in mm	450
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Number of phases	1

PUR 98 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting




EAN: 4002516717706 / Material number: 12358160 / Old Material Number: 28419855D

Total rated load in kW	0,22
Voltage in V	230
Fuse rating in A	10
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Accessories included	
Non-return flap	•

PUR 98 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



PUR92W Living, PUR98W, DA419-6, DA419-7 (Installation drawing)

1) Extraction, 2) Recirculation, 3) Ventilation grille at top for recirculation, 4+5) Installation cut-out (5 not required for recirculation)