

G 7180 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- Completely dry – Miele AutoOpen drying
- Fresh water dishwashers – as little as ?? water consumed in Automatic programme
- Very easy door opening and closing – ComfortClose

EAN: 4002516738367 / Material number: 12423740 / Old Material Number: 21718062GB

Available display languages

Available display languages via MultiLingua

bahasa malaysia, deutsch,
english (AU), english (GB),
[?][?][?][?][?][?], [?][?][?]

Model

Fully integrated dishwasher

•

60 cm dishwasher

•

Design

Control panel colour

Stainless Steel.

Control panel version

Fully integrated fascia

Control type

Programme selector
buttons

Display

1-line text display

Display colour

White

MultiLingua

•

Convenience

Networking with Miele@home

•

Automatic dispensing with PowerDisk

•

Door closing aid

AutoClose

Time left display

•

Delay start up to 24 hours

•

In-operation indicator light

optical and acoustic

Display language selection

•

Efficiency and sustainability

Energy efficiency class (A–G)

B

Water consumption in the Automatic programme in l from

6,0

Water consumption of the ECO programme in litres per
programme cycle

8,4

Electricity consumption in the ECO programme in kWh

0,64

Energy consumption of the ECO programme in kWh after
100 programme cycles

64

Consumption value in kWh in the ECO programme with
hot water connection

0,40

Duration of ECO programme in minutes

199

Noise emission class

B

Noise emissions in dB(A)

43

EcoFeedback

•

EcoPower Technology

•

Proven hygiene

•

Hot water connection

•

Half load

•

Quality of results

Fresh water dishwasher

•

AutoOpen drying

•

SensorDry

•

Active condensation drying

•

BrilliantGlassCare

•

Wash programmes

QuickPowerWash

•

G 7180 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738367 / Material number: 12423740 / Old Material Number: 21718062GB

| | |
|----------------------------------|-------------------|
| ECO | • |
| Automatic | • |
| ComfortWash 45 °C | • |
| Intensive 75 °C | • |
| PowerWash | • |
| ComfortWash+ 55 °C | • |
| Gentle | • |
| ExtraQuiet 39 dB(A) | • |
| Appliance care | • |
| Rinse out salt | • |
| Dishwashing options | |
| AutoDos | • |
| BottleClean | • |
| Quick | • |
| IntenseZone | • |
| Extra Clean | • |
| Extra dry | • |
| Basket design | |
| Cutlery loading | 3D MultiFlex tray |
| FlexCare glass holder | 2 |
| FlexCare cup rack | 1 |
| Basket design | ExtraComfort |
| Number of place settings | 14 |
| MultiClip | • |
| FlexCare Glass & Bottle | • |
| XL Assist | • |
| Safety | |
| Waterproof system | • |
| Filter indicator light | • |
| Technical data | |
| Niche width minimal in mm | 600 |
| Niche width max in mm | 600 |
| Niche height minimal in mm | 805 |
| Niche height maximal in mm | 870 |
| Niche depth in mm | 550 |
| Appliance width in mm | 598 |
| Appliance height in mm | 805 |
| Appliance depth in mm | 550 |
| Depth with door open in cm | 116,5 |
| Net weight in kg | 47,0 |
| Total rated load in kW | 2,00 |
| Voltage in V | 230 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Electrical frequency standard | 50 |
| Length of water inlet hose in cm | 1,50 |
| Length of water drain hose in cm | 1,50 |
| Length of supply lead in m | 1,80 |
| Min. front panel weight in kg | 4,0 |

G 7180 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.




EAN: 4002516738367 / Material number: 12423740 / Old Material Number: 21718062GB

| | |
|---|------|
| Max. front panel weight in kg | 11,0 |
| [can be retrofitted by Service to min.] | 7,0 |
| [can be retrofitted by Service to max.] | 14,0 |
| Accessories included | |
| 1 x PowerDisk | • |
| Voucher for 6 x PowerDisk | • |

G 7180 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),