

G 7210 SCi

Semi-integrated dishwasher
with 3D MultiFlex tray for maximum convenience.



- Best energy efficiency class A – energy-saving and eco-friendly
- Completely dry – Miele AutoOpen drying
- Perfect results in less than one hour – QuickPowerWash
- Fresh water dishwashers – as little as 6.0 l water consumed in Automatic programme
- Convenient, great results and perfect for everyday use – ExtraComfort baskets

EAN: 4002516738381 / Material number: 12423790 / Old Material Number: 21721057GB

Model	
Semi-integrated dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Stainless steel/CleanSteel
Control panel version	Straight fascia
Control type	Programme selector buttons
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Door closing aid	AutoClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
Efficiency and sustainability	
Energy efficiency class (A–G)	A
Water consumption in the Automatic programme in l from	6,0
Water consumption of the ECO programme in litres per programme cycle	8,4
Electricity consumption in the ECO programme in kWh	0,54
Energy consumption of the ECO programme in kWh after 100 programme cycles	54
Consumption value in kWh in the ECO programme with hot water connection	0,29
Duration of ECO programme in minutes	230
Noise emission class	B
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•
Gentle	•

G 7210 SCi

Semi-integrated dishwasher

with 3D MultiFlex tray for maximum convenience.



EAN: 4002516738381 / Material number: 12423790 / Old Material Number: 21721057GB

ExtraQuiet 39 dB(A)	•
Appliance care	•
Rinse out salt	•
Dishwashing options	
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
Number of place settings	14
MultiClip	•
FlexCare Glass & Bottle	•
XL Assist	•
Safety	
Waterproof system	•
Filter indicator light	•
Safety lock	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	570
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	570
Depth with door open in cm	116,5
Net weight in kg	48,2
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Min. front panel weight in kg	3,0
Max. front panel weight in kg	10,0
[can be retrofitted by Service to min.]	8,0
[can be retrofitted by Service to max.]	18,0
Accessories included	
Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•

G 7210 SCi
Semi-integrated dishwasher
with 3D MultiFlex tray for maximum convenience.




EAN: 4002516738381 / Material number: 12423790 / Old Material Number: 21721057GB

Available display languages	
Available display languages via MultiLingua	bahasa malaysia, deutsch, english (AU), english (GB), [?][?][?][?][?][?], [?][?][?]

G 7210 SCi

Semi-integrated dishwasher
with 3D MultiFlex tray for maximum convenience.



G7000, integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761)