

KS 4783 ED

Freestanding refrigerator

with DailyFresh and extra convenience for the perfect side-by-side combination.



- Spacious drawer with moisture control – DailyFresh
- Uniform temperature distribution inside the appliance – DynaCool
- Soft closing of the door with SoftClose
- Flexible refrigerator adaptation for tall containers – FlexiBoard
- Dishwasher-safe door shelves – ComfortClean

EAN: 4002516742289 / Material number: 12431300 / Old Material Number: 36478353AUS

|  |                       |
|--|-----------------------|
| <b>Appliance category</b>                                      |                       |
| Refrigerator   | •                     |
| <b>Construction type</b>                                       |                       |
| Freestanding appliance   | •                     |
| Door hinge   | right                 |
| Convertible door hinging                                       | •                     |
| Side-by-side enabled   | •                     |
| <b>Design</b>  |                       |
| Casing colour  | black                 |
| Front colour   | BlackSteel door       |
| Refrigeration section lighting                                 | LED                   |
| <b>User convenience</b>  |                       |
| Networking with Miele@home                                     | •                     |
| Freshness system   | DailyFresh            |
| ComfortClean   | •                     |
| DynaCool   | •                     |
| XL interior  | •                     |
| SoftClose  | •                     |
| Concealed door opener  | EasyOpen lever handle |
| <b>Control system</b>  |                       |
| Operating concept  | SensorTouch           |
| Precise adjustment   | Fridge temperature    |
| Independent temperature regulation of fridge and freezer zones | No                    |
| Automatic SuperCool  | •                     |
| No. of temperature zones                                       | 1                     |
| Sabbath mode   | •                     |
| Party mode   | •                     |
| Holiday mode   | •                     |
| <b>Fridge/Fridge section</b>                                   |                       |
| No. of shelves   | 6                     |
| including number of split shelves (FlexiBoard)                 | 1                     |
| Chrome-plated metal bottle rack                                | •                     |
| No. of crisper drawers   | 2                     |
| Number of inner door racks for tinned food                     | 3                     |
| Door rack for bottles  | 2                     |
| Door shelves   | 5                     |
| <b>Safety</b>  |                       |
| Lock function  | •                     |
| Acoustic door alarm  | •                     |
| Optical door alarm   | •                     |
| <b>Technical data</b>  |                       |
| Appliance width in mm  | 597                   |
| Appliance height in mm   | 1855                  |
| Appliance depth in mm  | 675                   |
| Weight in kg   | 68,9                  |
| Climate class  | SN-T                  |
| Total usable capacity in l                                     | 399                   |
| Current consumption (mA)                                       | 1200                  |
| Voltage in V   | 220-240               |

KS 4783 ED

Freestanding refrigerator

with DailyFresh and extra convenience for the perfect side-by-side combination.




EAN: 4002516742289 / Material number: 12431300 / Old Material Number: 36478353AUS

|                             |         |
|-----------------------------|---------|
| Fuse rating in A            | 10      |
| Number of phases            | 1       |
| Frequency in Hz             | 50-60   |
| Length of supply lead in m  | 2,0     |
| Replacing lamps             | Service |
| <b>Accessories included</b> |         |
| Egg tray                    | •       |

## KS 4783 ED


Freestanding refrigerator

with DailyFresh and extra convenience for the perfect side-by-side combination.




K4776ED, KS4783ED, FN4772E, installation sketch (footnote\*) (installation drawings)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.




KFN4777CD, KFN4797DD, KFN4797CD, KFN4799DDE, KFN4795DD, KFN4795CD, KFN4795BD, top view (footnote\*)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KS4783DD, KS4783ED, FNS4782E, FNS4782D, top view, Side-by-Side (\*footnote) (installation drawings)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KS4783DD, KS4383ED, FNS4782E, FNS4782D, installation sketch, Side-by-Side (\*footnote) (installation drawings)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.