

## G 7650 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Best energy efficiency class A – energy-saving and eco-friendly
- More information options and modern domestic appliance networking – Miele@home
- Incredibly low sound emissions of just ?? dB(A)
- Fresh water dishwashers – as little as ?? water consumed in Automatic programme
- Convenient, great results and perfect for everyday use – ExtraComfort baskets

EAN: 4002516798187 / Material number: 12569660 / Old Material Number: 21765062AE

<b>Model</b>	
Fully integrated dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	Obsidian Black
Control panel version	Fully integrated fascia
Control type	Softkeys
Display	1-line text display
Display colour	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
Operating noise dB(A) re 1 pW	43
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	optical and acoustic
Display language selection	•
<b>Efficiency and sustainability</b>	
FlexiTimer with EcoStart	•
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
<b>Wash programmes</b>	
QuickPowerWash	•
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•
Gentle	•
Hygiene	•
SolarSave	•
ExtraQuiet 37 dB(A)	•
Appliance care	•
Rinse out salt	•
<b>Dishwashing options</b>	
AutoDos	•

## G 7650 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516798187 / Material number: 12569660 / Old Material Number: 21765062AE

BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL Assist	•
<b>Safety</b>	
Waterproof system	•
Filter indicator light	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	550
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	550
Depth with door open in cm	116,5
Net weight in kg	48,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Energy stars	5,0
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Min. front panel weight in kg	4,0
Max. front panel weight in kg	11,0
[can be retrofitted by Service to min.]	7,0
[can be retrofitted by Service to max.]	14,0
<b>Available display languages</b>	
Available display languages through MultiLingua	deutsch, english, english (AU), [?][?][?][?][?][?], [?][?], [?][?]
<b>Accessories included</b>	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

## G 7650 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),