

G 7130 C SC AutoDos

Freestanding dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Cutlery tray with chopstick holder for maximum convenience – 3D MultiFlex
- More information options and modern domestic appliance networking – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Completely dry – Miele AutoOpen drying
- Very easy door opening and closing – ComfortClose

EAN: 4002516801429 / Material number: 12583170 / Old Material Number: 21713016SG

Available display languages	
Available display languages via MultiLingua	bahasa malaysia, deutsch, english (GB), [?], [?], [?]
Model	
Freestanding dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Brilliant White
Control panel version	Straight fascia
Control type	Programme selector buttons
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
Operating noise dB(A) re 1 pW	44
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
Efficiency and sustainability	
Drying class	A
Water consumption in the ECO programme in l	8,9
Annual water consumption in the ECO programme in l	2492
Annual energy consumption in ECO programme in kWh	192
Number of place settings	12
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•

G 7130 C SC AutoDos Freestanding dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516801429 / Material number: 12583170 / Old Material Number: 21713016SG

Gentle	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
Rinse out salt	•
Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray C
Chopstick holders	•
FlexCare glass holder	3
FlexCare cup rack	1
Basket design	ExtraComfort C
MultiClip	•
FlexCare Glass & Bottle	•
Safety	
Waterproof system	•
Filter indicator light	•
Safety lock	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119,5
Net weight in kg	56,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,80
Accessories included	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7130 C SC AutoDos
Freestanding dishwashers
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, free standing dishwasher, 60cm (installation drawing)